

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2002

© COPYRIGHT 2002


BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	NEW GLASS FIBER PERCENTAGE ON HSG ECR-15-3187	18JAN2005	A.B.	M.G.
	C1	ECR15-011013	29JUL2015	M.P.	M.G.
	C2	REVISED PER ECO-17-001706	10FEB2017	C.A.	M.G.

SLITTA IN POSIZIONE APERTA
(SLIDE IN OPEN POSITION)




SLITTA IN POSIZIONE CORRETTA PER ACCOPPIAMENTO DI CONNETTORE CON CONTROPARTE
(SLIDE IN PROPER POSITION TO MATE THE CONNECTOR WITH COUNTERPART)


C.P.A. IN POSIZIONE CHIUSA
(C.P.A. IN CLOSED POSITION)




VERSIONE SENZA C.P.A.
(POLARIZZAZIONI -2 E -4)
VERSION WITHOUT C.P.A.
(POLARIZATION -2 AND -4)




SECTION C-C






VISTA ESPLOSA
(EXPLODED VIEW)


STATO DI FORNITURA
(SUPPLYING CONDITION)



P/N 284853-1 COME MOSTRATO (CODICE A)
(P/N 284853-1 AS SHOWN (CODING A))
VEDI FOGLIO 2 PER ALTRE POLARIZZAZIONI
(SEE SHEET 2 FOR OTHER POLARIZATIONS)

SECONDARY LOCK FORNITO NELL' IMBALLO IN PARI QUANTITA'
(SECONDARY LOCK SUPPLIED IN THE BOX IN THE SAME Q.TY)





SCALE 2:1

I	GIALLO/ (YELLOW)	PA66 GF13	C.P.A. (OPZIONALE) C.P.A. (OPTIONAL)	4
I	ROSSO/ (RED)	PA66 GF30	SECONDARY LOCK	3
I	BLU/ (BLUE)	PA66 GF30	SLITTA/ (SLIDE)	2
I	NERO O GRIGIO (BLACK OR GREY)	PA66 GF13	BLOCCHETTO/ (HOUSING)	1
Q.TA' (Q.TY)	COLORE (COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	NO. (ITEM)

1) IL CONNETTORE SI ACCOPPIA CON LA CONTROPARTE P/N 284858
(CONNECTOR MATEABLE WITH COUNTERPART P/N 284858)

2) N.RO 4 CAVITA' ADATTE PER CONTATTI FEMMINA AMP MCP 2.8 STAGNATI
(Nr 4 CAVITIES SUITABLE FOR AMP MCP 2.8 SOCKET CONTACTS TIN PLATED)
P/N 1241388-1: ADATTO PER RANGO FILO 0.5-1.0sqmm
(SUITABLE FOR 0.5-1.0sqmm WIRE SECTION)
P/N 1241390-1: ADATTO PER RANGO FILO >1.0-2.5sqmm
(SUITABLE FOR >1.0-2.5sqmm WIRE SECTION)

3) N.RO 8 CAVITA' ADATTE PER CONTATTI FEMMINA AMP MCP 1.5 STAGNATI
(Nr 8 CAVITIES SUITABLE FOR AMP MCP 1.5 SOCKET CONTACTS TIN PLATED)
P/N 1241372-1: ADATTO PER RANGO FILO 0.2-0.35sqmm
(SUITABLE FOR 0.2-0.35sqmm WIRE SECTION)
P/N 1241374-1: ADATTO PER RANGO FILO 0.5-1.0sqmm
(SUITABLE FOR 0.5-1.0sqmm WIRE SECTION)
P/N 1534334-1: ADATTO PER RANGO FILO >1.0-1.5sqmm
(SUITABLE FOR >1.0-1.5sqmm WIRE SECTION)

4) IL CONNETTORE VIENE FORNITO CON SLITTA IN POSIZIONE CHIUSA; IL DISPOSITIVO DI AGGANCIO SECONDARIO VIENE FORNITO IN KIT NELLA STESSA SCATOLA IN PARI QUANTITA'
(CONNECTOR IS SUPPLIED WITH SLIDE IN CLOSED POSITION; SECONDARY LOCK IS SUPPLIED IN KIT IN THE SAME BOX AND QUANTITY)

5) C.P.A. IN POSIZIONE PREASSEMBLATA (C.P.A. IN PREASSEMBLED POSITION)

6) C.P.A. IN POSIZIONE CHIUSA, QUANDO IL CONNETTORE E' CORRETTAMENTE ACCOPPIATO CON LA CONTROPARTE
(C.P.A. IN CLOSED POSITION, WHEN THE CONNECTOR IS PROPERLY MATED WITH THE COUNTERPART)

7) AGGANCIO SECONDARIO COMPLETAMENTE INSERITO, DOPO AVER POSIZIONATO I CONTATTI IN CAVITA'
(SECONDARY LOCK COMPLETELY MOUNTED, AFTER CONTACTS INSERTION INTO CAVITIES)

8) LE POLARIZZAZIONI -2 E -4 DIFFERISCONO DALLE -1 E -3 SOLAMENTE PER LA SEDE DEL C.P.A. OCCLUSA
(POLARIZATION KEYS -2 AND -4 ARE DIFFERENT FROM -1 AND -3 ONLY FOR THE OCCLUDED SEAT FOR C.P.A.)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3
1 PLC ±0.2
2 PLC ±0.1
3 PLC ±
4 PLC ±
ANGLES ±°

FINISH
SEE TABLE

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
A. PLAZIO 03MAY2002

CHK
C. PIA 06MAY2002

APVD
A. GENIA 06MAY2002

PRODUCT SPEC
108-20243

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

NAME
AMP MCP 1.5/2.8 SOCKET HOUSING
12 POS. ASS'Y-UNSEALED
(CONNETTORE IBRIDO 12 VIE)

SIZE
A2

CAGE CODE
-

DRAWING NO
C-284853

RESTRICTED TO
-

SCALE
NO SCALE

SHEET
1 OF 2

REV
C2

1471-9 (3/13)

