



**BOURNS®**

## Features

- Surface Mount Device
- Reduced footprint size
- High voltage surge capabilities
- Assists in meeting ITU K.20/K.21/K.45 specifications
- RoHS compliant\*
- Agency recognition:   

## Applications

- Provides overcurrent protection in:
- Customer Premise Equipment (CPE)
- Central Office (CO)
- Access/Outside Plant Equipment

## MF-SM013/250V - Telecom PTC Resettable Fuses

### Electrical Characteristics

Model	Max. Operating Voltage Volts	Max. Interrupt Ratings		Hold Current	Initial Resistance		One Hour Post-Trip Resistance	Tripped Power Dissipation
		Volts (V)	Amps (A)		Amps at 23 °C	Ohms at 23 °C		
		Max.	Max.	I <sub>H</sub>	Min.	Max.	Max.	Typ.
MF-SM013/250V	60	250	3.0	0.13	6.5	12.0	20.0	3.0
MF-SM013/250V-B05-2	60	250	3.0	0.13	9.0	12.0	20.0	3.0

### Environmental Characteristics

Operating Temperature .....	-40 °C to +85 °C
Maximum Device Surface Temperature in Tripped State .....	125 °C
Passive Aging .....	+85 °C, 1000 hours.....+60 °C, 1000 hours.....
Humidity Aging .....	+85 °C, 85 % R.H. 500 hours.....
Thermal Shock .....	MIL-STD-202F, Method 107G, +125 °C to -55 °C, 10 times.....
Solvent Resistance .....	MIL-STD-202, Method 215B.....
Lead Solderability .....	ANSI/J-STD-002
Flammability .....	IEC 695-2-2.....
Vibration .....	MIL-STD-883C, Method 2007.1, Condition A .....

### Test Procedures And Requirements For Model SM013/250V Series

Test	Test Conditions	Accept/Reject Criteria
Visual/Mech.	Verify dimensions and materials.....	Per MF physical description
Resistance .....	In still air @ 23 °C .....	R <sub>min</sub> ≤ R ≤ R <sub>max</sub>
Time to Trip .....	At specified current, V <sub>max</sub> , 23 °C .....	T ≤ max. time to trip (seconds)
Hold Current .....	30 min. at I <sub>hold</sub> .....	No trip
Trip Cycle Life .....	V <sub>max</sub> , I <sub>max</sub> , 100 cycles .....	No arcing or burning
Trip Endurance .....	V <sub>max</sub> , 48 hours.....	No arcing or burning
Solderability .....	MIL-STD-202F, Method 208F .....	95 % min. coverage
UL File Number .....	E 174545S	
CSA File Number .....	CA 110338	
TÜV File Number .....	R2057213	

### Thermal Derating Chart -I<sub>hold</sub> / I<sub>trip</sub> (Amps)

Model	Ambient Operating Temperature								
	-40 °C	-20 °C	0 °C	23 °C	40 °C	50 °C	60 °C	70 °C	85 °C
MF-SM013/250V	0.21 / 0.42	0.18 / 0.37	0.16 / 0.31	0.13 / 0.26	0.10 / 0.23	0.09 / 0.18	0.08 / 0.15	0.07 / 0.12	0.05 / 0.10



\*RoHS Directive 2002/95/EC Jan 27 2003 including Annex

Specifications are subject to change without notice.


Customers should verify actual device performance in their specific applications.

# MF-SM013/250V Series - Telecom PTC Resettable Fuses **BOURNS®**


## Product Dimensions



### Recommended Pad Layout




DIMENSIONS =  $\frac{\text{MM}}{(\text{INCHES})}$



Terminal material:  
Tin-plated brass

Packaging:  
TAPE & REEL: 1000 pcs. per reel

## Solder Reflow Recommendations



### Solder reflow

- Recommended reflow methods: IR, vapor phase oven, hot air oven.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Gluing the devices is not recommended.
- Recommended maximum paste thickness is 0.25 mm (.010 inch).
- Devices can be cleaned using standard industry methods and solvents.

### Note:

- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

### Rework


- A device should not be reworked.

## Storage Recommendations

The recommended long term storage conditions for Multifuse® Polymer PTC devices are 40 °C maximum and 70 % RH maximum. All devices should remain in the original sealed packaging prior to use. Devices may not conform with data sheet specifications if these storage recommendations are exceeded. Devices stored in this manner have an indefinite shelf life.


# MF-SM013/250V Series - Telecom PTC Resettable Fuses **BOURNS®**

## Typical Time to Trip at 23 °C



## Typical Part Marking

Represents total content. Layout may vary.



## How to Order

### MF - SM 013/250V - B 05 - 2

Multifuse®  
Product Designator  
Series  
SM = Surface Mount Component  
Hold Current,  $I_{hold}$   
013 = 0.13 Amps  
Max. Interrupt Voltage, V  
250 = 250 Volts  
Telecom Options  
V = Vertical Profile  
(Surface Mount Products Only)  
Resistance Sorted  
Narrow resistance range  
available upon request  
Resistance Bins  
05 = 0.5 ohms  
Packaging Options  
- 0 = Bulk Packaging  
- 2 = Tape and Reel\*

\*Packaged per EIA486-B