


Delock Adapter Sub-D 25 Pin Stecker > Terminalblock 27 Pin

Kurzbeschreibung

Über diesen Sub-D zu Terminalblock Adapter von Delock können Litzen mit abisolierten Enden angeschlossen werden. Dadurch ist der Adapter nicht nur für spezielle Industrieanwendungen, z.B. für Service-, Mess - und Prüfzwecke geeignet, sondern kann auch im Hobbybereich, wie dem Eisenbahnmodellbau, angewendet werden.



Technische Daten

- Sub-D 25 Pin Stecker
- 3 x 9 Pin Terminalblock (25 Pins beschaltet)
- Pitch 3.81 mm
- Stecker mit Schrauben
- Maße (LxBxH): 54,2 mm x 53,04 mm x 16,05 mm

Artikel-Nr. 65318



EAN 4043619653188

Ursprungsland China

Packungsinhalt

- Adapter


Verpackung

- Poly Bag

Delock Adapter Sub-D 25 pin male > Terminal Block 27 pin

Description

This Sub-D to terminal block adapter is made for special industrial application e.g. for connecting single wires with open cable heads. It also can be used in the hobby area for example for model railroading.



Specification

- Sub-D 25 pin male
- 3 x 9 pin terminal block (25 pins connected)
- Pitch 3.81 mm
- Male port with screws
- Dimension (LxWxH): 54.2 mm x 53.04 mm x 16.05 mm

Item No. 65318



EAN 4043619653188

Country of origin China





Package content

- Adapter

Package

- Poly bag


WIRING TABLE	
DB25 PIN #	TERMINAL PIN #
1	1
2	2
3	3
4	4
5	5
6	6
.....	
.....	
.....	
20	20
21	21
22	22
23	23
24	24
25	25
SHELL	SHL



Part name:
Adapter terminal block > Sub-D 25 pin Male

Electrical Character:

- 1> 100% open&short testing
- 2> With understanding voltage:DC 500 V 0.01 Sec.
- 3> Insulation Resistance: 50M Ohm (Min)
- 4> Conductive Resistance: 2 Ohm(Max)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN mm	APPROVALS	DATE	 we move the world
	DRAWN BY May	7/11/2011	
	CHECKED BY Gang	7/11/2011	
	APPROVED BY Steven	7/12/2010	
DIMENSIONAL TOLERANCES: .X = ±0.3 .XX = ±0.2 .XXX = ±0.1	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		Item no. 65318
ANGULAR TOLERANCES: ALL = ± 1°	PROJECTION 		Barcode: 4043619653188
			File: 88072
	COLOR VARIATIONS MAY OCCUR		