


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		J2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



1. REELED FOR MINI APPLICATOR.
- 3 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 4 .000015 GOLD ON CONTACT AREA, .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN CRIMP AREA K, ALL OVER .000050 NICKEL.
- 5 .000030 GOLD ON CONTACT AREA, .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN CRIMP AREA K, ALL OVER .000050 NICKEL.
- 6 SHEARED EDGES PERMITTED TO BE UNPLATED.
- 7 .000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL.
- 8 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 9 OBSOLETE PART NUMBER
- 10 SUPERCEDED BY 103171-5.
- 11 .000015 GOLD ON CONTACT AREA, MATTE TIN IN CRIMP AREA K, ALL OVER .000050 NICKEL.
- 12 .000030 GOLD ON CONTACT AREA, MATTE TIN IN CRIMP AREA K, ALL OVER .000050 NICKEL.
- 13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5-103171-5	12 6	5-103171-4
13 5-103171-2	11 6	5-103171-1
9 -8	6 7	9 -7
103171-5	5 6	103171-4
103171-2	4 6	103171-1
LOOSE PIECE PART NO	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	31 MAR 83	TE Connectivity				
DIMENSIONS: INCHES		CHK —	—	NAME CONTACT, RECEPTACLE, MOD IV 1/2 CRIMP SNAP-IN FOR 22-26 AWG WIRE				
		APVD —	11 APR 83					
		PRODUCT SPEC —						
		APPLICATION SPEC —						
MATERIAL CU-SN-P ALLOY 521 .008 THK. COMPL.		FINISH		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-103171	RESTRICTED TO —
SEE TABLE		CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV J2	