




VIEWED FROM FRONT OF FOOTSWITCH

NOTE:
FOR EARTHING METHODS
REFER TO 5031-136

(07) (08)

SCALE :- NTS				
FIRST USED ON :- 6289-SB				
TOOL No. :-				
REV.	CHANGE NOTE	CHANGE BY	DATE	CHECKED BY
06	CN7282	DB	26/06/00	
07	CN12421	MJC	13/06/07	
08	CN14053	MJC	07/12/10	MH

THIS DOCUMENT IS THE PROPERTY OF HERGA ELECTRIC LTD
AND SUPPLIED IN CONFIDENCE.
IT MUST NOT BE REPRODUCED OR DISCLOSED TO A THIRD PARTY
WITHOUT THE WRITTEN CONSENT OF HERGA ELECTRIC LTD

herga electric Ltd
NORTHERN WAY, BURY ST EDMUNDS,
SUFFOLK, ENGLAND, IP32 6NN
www.herga.com
TEL :- 01284 701422
FAX :- 01284 753112

UNLESS OTHERWISE STATED ALL DIMENSIONS IN mm GENERAL
TOLERANCES :-
± 30 MINUTES ON ANGULAR DIMS
± 0.5 ON DIM. WITH NO DECIMAL PLACE
± 0.3 ON DIM. WITH ONE DECIMAL PLACE
± 0.1 ON DIM. WITH TWO DECIMAL PLACES

PROJECTION		DO NOT SCALE - IF IN DOUBT ASK					
STRAIGHTNESS		PARALLELISM		CONCENTRICITY		LINE PROFILE	
FLATNESS		SQUARENESS		M.M.C		SURFACE PROFILE	
ROUNDNESS		ANGULARITY		RUN OUT		SYMMETRY	
CYLINDRICITY		POSITION		SURFACE FINISH			

MATERIAL :-
FINISH :-
SHRINKAGE :-

TITLE :-
WIRING DIAGRAM
5020-044