

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 773951



Features

- Low profile
- Rugged design
- Vertical or horizontal entry
- Tape & reel packaging available
- RoHS compliant*

70AD/Male - Modular Contact

Materials & Finishes

Insulator.....Glass reinforced thermoplastic, UL 94V-0 rated, black
 Contact.....Copper alloy
 Finish
 Underplating.....30 μ " - 60 μ " nickel
 Contact Area.....30 μ " Au over Ni
 Termination.....Tin alloy
 (meets MIL-STD-202, method 208)

Operating Characteristics

Electrical

Current Rating.....DC 3 A/contact
 Voltage RatingDC 30 V
 Contact Resistance.....25 m Ω max.
 Dielectric Voltage.....AC 500 V
 Insulating Resistance500 M Ω min.
 Operating Temperature
-55 $^{\circ}$ C to 125 $^{\circ}$ C

Mechanical

Vibration.....10-55 Hz, 0.06 inches D.A.
 Shock50 G, 11 ms
 Normal Force100 grams min.
 at a working height of
 0.51 mm (0.020 in.)
 Durability.....5,000 cycles

Patent No. 5,378,160.

How to Order





70AD J - 3 - M L 0 G

Model _____
 Terminal Style _____
 J = SMT
 H = Through-hole
 Number of Contacts _____
 2 through 6
 Gender _____
 M = Male
 Height _____
 L = Low Profile
 Options _____
 0 = Standard
 1 = Locator Pins (J style only)
 Packaging Option _____
 — = Tube (240/N pcs. or 240 contacts per tube)
 G = Embossed Tape (500 pcs. per reel)


Number of Contacts	Dimension A	Dimension B
2	$\frac{7.7}{(.303)}$	$\frac{5.11}{(.201)}$
3	$\frac{11.7}{(.461)}$	$\frac{9.11}{(.359)}$
4	$\frac{15.7}{(.618)}$	$\frac{13.11}{(.516)}$
5	$\frac{19.7}{(.776)}$	$\frac{17.11}{(.674)}$
6	$\frac{23.7}{(.933)}$	$\frac{21.11}{(.831)}$

Product Dimensions




70ADJ




RECOMMENDED PWB MOUNTING PATTERN



70ADH



RECOMMENDED PWB PCB HOLE PATTERN



DIMENSIONS ARE: $\frac{\text{MM}}{(\text{INCHES})}$

TOLERANCES: + 0.30 (0.012)

REV. 01/06

*RoHS Directive 2002/95/EC Jan 27 2003 including Annex.
 Specifications are subject to change without notice.
 Customers should verify actual device performance in their specific applications.