


LOC	DIST	REVISIONS					
F	7	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P	REVISED PER ECO-11-005150	21MAR11	RK	HMR


- 1

SENS DE BOBINAGE STANDARD (POUR APPLICATEUR STANDARD).
- 2


SENS DE BOBINAGE INVERSE (POUR MINI-APPLICATEUR).



CONTACT EN VRAC



					DIMENS. FIL VOIR CI-DESSUS		ISOLANT -	
28-32	0.5-1.0	DORE 0.8µM DANS LA ZONE DE CONTACT FLASH D'OR SUR LE RESTE SOUS-COUCHE 1.27µM NI.	11.7	0-167023-2		0-167020-2		
						-		
28-32	0.5-1.0	DORE 0.8µM DANS LA ZONE DE CONTACT ETAIN SUR LE FUT SOUS-COUCHE 1.27µM NI.	11.7	0-167023-1		0-167020-1		
						-		
20-26 (0.5mm ² MAX)	1.40 MAX	DORE 0.8µM DANS LA ZONE DE CONTACT ETAIN SUR LE FUT SOUS-COUCHE 1.27µM NI.	12.3	0-141603-4		0-167300-8		
						0-167300-7		
20-26 (0.5mm ² MAX)	1.40 MAX	DORE 0.8µM DANS LA ZONE DE CONTACT FLASH D'OR SUR LE RESTE SOUS-COUCHE 1.27µM NI.	12.3	0-141603-3		0-167300-6		
						0-167300-5		
JAUGE AWG FIL	DIAMETRE ISOLANT (MM)	FINITION	DIM 'A'	REFERENCE CONTACT EN VRAC	REFERENCE CONTACT EN BANDE			

DIMENSIONS: mm		DWN A.CAMEL	20.MAR.89	MATERIAL BRONZE PHOSPHOREUX	FINISH VOIR CI-DESSUS
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK —	—	 TE Connectivity	
0 PLC ± —		APVD —	—		
1 PLC ± 0.3		PRODUCT SPEC —	—		
2 PLC ± —		APPLICATION SPEC —	—	NAME CONTACT AMPMODU MOD.IV	
3 PLC ± —		—	—	SIZE A4	CAGE CODE 00779
4 PLC ± —		—	—	DRAWING NO C-141603	RESTRICTED TO —
ANGLES ± 5°		—	—	SCALE 5:1	
		WEIGHT —	—	SHEET 1 OF 1	REV P
CUSTOMER DRAWING					