


10	9	8	7	6	5	4	3	2	1
MATERIAL NO. LOOSE PIECE	ENGINEERING NO. LOOSE PIECE	MATERIAL NO. TAPE MOUNTED	ENGINEERING NO. TAPE MOUNTED	AWG	"I.D." MIN	"B" MIN	"L" MAX	"P" MIN	"D" ± $\frac{.01}{0.3}$
192110003	WP-1218	192110004	WP-1218 T	22-18	.054/1.37 (G2)	.165/ 4.19	.68/ 17.3	.35/ 8.9	.078/ 1.98
192110005	WP-1614	192110006	WP-1614 T	16-14	.081/2.06	.165/ 4.19	.68/ 17.3	.35/ 8.9	.078/ 1.98
192110001	WP-1210	192110002	WP-1210 T	12-10	.128/3.25	.230/ 5.84	.82/ 20.8	.41/ 10.4	.107/ 2.72



NOTES:

1. MATERIAL: COPPER
2. FINISH: ELECTRO-TIN PLATING
3. PARTS ARE ROHS COMPLIANT.

SALES DRAWING

ID TOLERANCE 22-18		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
EC NO: 2010/11/17		▼=0		mm INCH		DRAWN BY DATE		TITLE			
DRW:ETHRODAHL		▽=0		4 PLACES ± --- ± ---		B. ENDERLE 02/14/02		KRIMPTITE WIRE PIN			
CHKD: JMACNEIL				3 PLACES ± --- ± ---		CHECKED BY DATE		TERMINALS			
APPR:				2 PLACES ± --- ± ---		H. BIETZEL 02/14/02		22-18, 16-14, 12-10 AWG			
				1 PLACE ± --- ± ---		APPROVED BY DATE		MOLEX MOLEX INCORPORATED			
				ANGULAR ± ---°		JMACNEIL 2010/03/18		DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-19211-002		1 OF 1	
REV						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
G2											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19211-0001](#) [19211-0002](#) [19211-0005](#) [19211-0004](#)