


REVISIONS				DOC. NO. SPC-F005, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
129	A	RELEASED	DJC	5/11/98	JC	7/15/98	JWM



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 500 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-7 GHz

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
8	SHELL	1	BRASS	NICKEL
7	RETAINING RING	1	BRASS	NONE
6	GASKET	1	S.I. RUBBER	RED
5	GROUND RING	1	BRASS	NICKEL
4	DIELECTRIC	1	TEFLON	NONE
3	DIELECTRIC	1	TEFLON	NONE
2	CONTACT	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.				DRAWING TITLE: TNC FEMALE TO N MALE							
DRAWN BY: DANIEL CAREY		DATE: 3/11/98		SIZE A		DWG. NO. 1542		ELECTRONIC FILE 92N3388.DWG		REV A	
CHECKED BY: JOHN COLE		DATE: 7/15/98		SCALE: NTS		U.O.M.: INCHES [mm]		SHEET: 1		OF 1	
APPROVED BY: JEFF MCVICKER		DATE: 7/15/98									

SPC-FD015.DWG