

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

Fiber Optic Products**➡ Transceivers and Data Links****AMP****269087-1**[Obsolete](#)[Not Reviewed for ELV/RoHS Compliance](#)**(Tyco Electronics P/N: 269087-1)**

Contact the [Product Information Center](#) to obtain the replacement part number.

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
✦ General Info ✦ Sales Info ✦ Assembly Subcontractors	✦ Pricing ✦ Product Availability	✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Transmitter Performance
Specification](#)
[Receiver Performance
Specification](#)
[Absolute Maximum
Ratings](#)
[Absolute Maximum
Ratings](#)
Searchable Features:

Brand:	AMP
Product Type:	Transceiver
No. of Pins:	9
Application:	Fast Ethernet, FDDI
Data Rate (Mb/s):	125
Transceiver/Data Link Style:	SC Duplex Laser
Power Supply:	Without

Other Properties:

FDDI SMF PMD Layer Requirement:	Category 1
Fiber Size (Micron):	10
Optical Wavelength (nm):	1300
Distance [Max.] (km):	10.000
Color:	Black
Process Plug:	269108-1

[Copyright](#) and [Privacy Statement](#)

 Visit [Tyco International, Ltd.](#)
[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)