

Antenna cable - RAD-PIG-EF316-MCX-SMA - 2867678

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Adapter cable, pigtail 100 cm MCX (male) -> SMA (male), insertion attenuation 1.5 dB at 2.4 GHz; impedance 50 ohms;



Product Features

- ✓ As an adapter between devices and cables

Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	32.8 GRM
Custom tariff number	85442000
Country of origin	Poland

Technical data

Dimensions

Fixed cable length	100 cm
External diameter	2.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Connection 1	Connector connection
Connection method	MCX (male)
Connection 2	Connector connection
Connection method	SMA (male)
Cable type	EF 316
Cable, attenuation	approx. 1.5 dB/m
	approx. 0.83 dB/m for 900 MHz
	approx. 1.27 dB/m for 1.8 GHz
	approx. 1.52 dB/m for 2.4 GHz

Antenna cable - RAD-PIG-EF316-MCX-SMA - 2867678

Technical data

General

	approx. 2.48 dB/m for 5 GHz
Outer sheath, material	RADOX®(LSFH)
Minimum bending radius	12.50 mm

Classifications

eCl@ss

eCl@ss 4.0	27060805
eCl@ss 4.1	27060805
eCl@ss 5.0	27061805
eCl@ss 5.1	27061805
eCl@ss 6.0	27061805
eCl@ss 7.0	27061805
eCl@ss 8.0	27061805

ETIM

ETIM 2.0	EC000019
ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC000019

UNSPSC

UNSPSC 6.01	26121608
UNSPSC 7.0901	26121608
UNSPSC 11	26121608
UNSPSC 12.01	26121608
UNSPSC 13.2	26121608