


FEED DIRECTION



— DIE-CUT THRU
TYP. (SOLID LINE)

— PERFORATION
.010 CUT, .0007" TIE
TYP.



PANDUIT PART NO.	MATERIAL	A	B	C	E	LABELS/ROLL
C150X030Y1C	GMY2	1.13	0.300	1.500	0.250	100
C195X040Y1C	GMY2	0.85	0.400	1.950	0.300	100
C261X035Y1C	GMY2	0.85	0.350	2.610	0.265	75
C282X030Y1C	GMY2	0.85	0.300	2.820	0.305	75
C288X040Y1C	GMY2	0.85	0.400	2.875	0.250	75
C390X030Y1C	GMY2	0.85	0.300	3.900	0.350	50
C750X050Y1C	GMY2	0.85	0.500	7.500	0.250	30
C788X050Y1C	GMY2	0.85	0.500	7.875	0.250	30

									CAD FILENAME/LAYERS	I00743NE_C I0454_CxxxXxxxYIC_00.prt
									PANDUIT	CORP TINLEY PARK, ILLINOIS
									CUSTOMER DRAWING LS8 COMPONENT LABELS C***X***YIC (SMALL LABEL GAP)	
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: .XXI ± .030 (.XXX) ± .005 .XXI ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
1	5-11-07	PSG		ADDED NEW PART NUMBER C15OX03OYIC	4987	R			DRAWN BY RVU	MAT'L:
O	8-29-06	RVU		DRAWING RELEASE	4670	R			DATE 8-29-06	SEE TABLE
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	CHK'D	DWG B SIZE