

Part # 813, 24 AWG Standed Topcoat Copper Wire UL Style UL 1007/ UL Style 1569, Consolidated Hook Up Wire



24 AWG Standed Topcoat Copper Wire UL Style UL 1007/ UL Style 1569, Consolidated Hook Up Wire

- Product Construction**
24 AWG Topcoat Copper Wire
- Conductor:**
24 AWG Stranded Topcoat Copper Wire Conductor per ASTM B-33
- Insulation:**
Color coded PVC
Temperature: UL 1007, -40°C to +80°C
Temperature: UL 1569, -40°C to +105°C
Voltage Rating: 300 volts
- Applications:**
Dual Rating UL Style 1007 and UL Style 1569
Hook-Up wire
Point to point wiring
Internal wiring of meters, panels, electrical and electronic equipment
- Industry Approvals:**
UL Style 1007
UL Style 1569
CSA-TR-64
VW-1
RoHS Compliant
OSHA acceptable
- Packaging:**
1000 ft. spools
100 ft. spools
Also available on bulk reels

· [SPECIFICATIONS](#) · [OTHER INFORMATION](#)

SPECIFICATIONS

Gauge	24 AWG
Strands	7 x 32 Topcoat Wire
Nominal Insulation Wall	0.016 in.
Insulation Type	PVC
Nominal O.D.	0.057 in.

Color	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
Color Code Chart	Chart-Hook-Up Wire
Insulation Temperature	-40°C to +80°C / -40°C to +105 °C
Voltage Rating	300 V
Disclaimer	<p>Terms and Conditions for the Consolidated Electronic Wire and Cable Website:</p> <p>Consolidated has made a very reasonable effort to ensure the accuracy of this "website" pertaining to the information, specifications and the "search" accuracy. The "website" is subject to errors and omissions. The content is subject to change without notice. This "website" is being constantly updated to correct any errors and omissions, but this does not ensure it is completely accurate. Drawings are for general reference only.</p> <p>Consolidated Electronic Wire & Cable is not liable for any direct, indirect, incidental or consequential damages resulting from the use of the material from this "website".</p>

OTHER INFORMATION

Approvals	<p>CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1</p>
-----------	--