



- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE — 16 OUNCES MIN INITIALLY.
6 OUNCES MIN AFTER 500 CYCLES.
- ③ REFER TO MOUNTING HOLE PATTERN.
- ④ .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.



HOUSING — MATERIAL; COLOR		RECEPTACLE — MATERIAL; FINISH		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13APR2004 M.S. FEHER CHK 13APR2004 E. HOWARD APVD 13APR2004 E. HOWARD		 TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME ASSEMBLY, TEST PROBE			
	0 PLC ± — 1 PLC ± — 2 PLC ± .015 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC —		—	
		APPLICATION SPEC —		—	
		SIZE A2	CAGE CODE 00779	DRAWING NO C-582118	RESTRICTED TO —
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —			
		CUSTOMER DRAWING		SCALE 6:1	SHEET 1 of 1
				REV AB2	