



Headers

to Type 213

	Type 178	page 148
	Type 179	page 144
	Type 219	page 143
	Type 220	page 144
	Type 229	page 147
	Type 230	page 148

to Type 214

	Type 178	page 148
	Type 179	page 144
	Type 219	page 143
	Type 220	page 144
	Type 229	page 147
	Type 230	page 148
	Type 286	page 146
	Type 288	page 150
	Type 290	page 146
	Type 292	page 150

Accessories

for Type 213 and Type 214
(only in combination with
headers type 178, 179, 219,
220, 229 and 230)

Coding set

700025 page 206



Type 213

Screw type terminal block, pluggable, centerline
5.08 mm / 0.200 inches, wire entry on rippled side,
perpendicular to plug direction, lift system, contact
with integrated wire protection

Technical Data

V / A / AWG 300 / 12 / 28 - 12

0.08 - 2.5 mm² 250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according
to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.



L = (pole size - 1) x centerline + 5.08 mm / 0.200 inches

Part numbers (P/N)

(information: page 56)

Complete the part number by
adding the pole size.

Type 213

centerline 5.08 mm / 0.200 inches

P/N 312131

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 213

centerline 10.16 mm / 0.400 inches

P/N 312132

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000
pieces per item.

Type 214

Screw type terminal block, pluggable, centerline
5.08 mm / 0.200 inches, wire entry on straight side,
perpendicular to plug direction, lift system, contact
with integrated wire protection

Technical Data

V / A / AWG 300 / 12 / 28 - 12

0.08 - 2.5 mm² 250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.2 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according
to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.



L = (pole size - 1) x centerline + 5.08 mm / 0.200 inches

Part numbers (P/N)

(information: page 56)

Complete the part number by
adding the pole size.

Type 214

centerline 5.08 mm / 0.200 inches

P/N 312141

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 214

centerline 10.16 mm / 0.400 inches

P/N 312142

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000
pieces per item.