






DO NOT
SCALE FROM
THIS PRINT

FIG 1

[FHP-10-02-X-S SHOWN]



-LC OPTION



-A OPTION

TABLE 1


FINISHED GOODS	SUB ASSEMBLY
FHP-02-02-T-S-XX	FHP-24-02-T-S-02
FHP-02-01-T-S-XX	FHP-24-01-T-S-02
FHP-03-02-T-S-XX	FHP-24-02-T-S-03
FHP-04-01-T-S-XX	FHP-24-01-T-S-04
FHP-04-02-T-S-XX	FHP-24-02-T-S-04
FHP-05-02-T-S-XX	FHP-24-02-T-S-05
FHP-06-01-TM-S-XX / T-S-XX	FHP-24-01-T-S-06
FHP-08-01-T-S-XX	FHP-24-01-T-S-08
FHP-10-02-T-S-XX / TM-S-XX	FHP-24-02-T-S-10
FHP-12-02-T-S-XX	FHP-24-02-T-S-12
FHP-13-01-T-S-XX	FHP-24-01-T-S-13
FHP-14-01-T-S-XX	FHP-24-01-T-S-14
ALL REMAINING CONFIGURATIONS	FHP-24-XX-X-S

FIG 2

-LC & -A OPTIONS

[-LC & -A OPTIONS ONLY AVAILABLE ON -02 LEAD STYLE]
(SAME AS FIG 1, UNLESS OTHERWISE STATED)

FHP-XX-XX-XX-S-XX-XX

No OF POSITIONS
-02 THRU -24
(PER ROW)
[SEE POSITIONAL FILL VIEW]LEAD STYLE
-01: THROUGH HOLE
(USE C-130-01-X)
-02: SURFACE MOUNT
(USE C-130-02-X)*POLARIZATION
-02 THRU -06, -08, -10, -12, -13 & -14
(SEE TABLE 1 FOR AVAILABLE COMBINATIONS)
(SEE SHT 3, IN-PROCESS 1 POLARIZED FILL)
(SEE NOTE 12)OPTION
-TR: TAPE & REEL PACKAGING
(T&R AVAILABLE FOR 2 THRU 18 POS)
(SEE NOTES 6 & 10)OPTION
-LC: LOCKING CLIP (USE LC-05-TM)
(-02 LEAD STYLE ONLY, SEE NOTE 11)
-A: ALIGNMENT PIN (USE FHP-XX-S-A)
(SEE FIG 2) (-02 LEAD STYLE ONLY)
-K: POLYIMIDE FILM PAD
(SEE FIG 3, SHT. 2) (USE K-DOT-.256-.375-.005)
(-02 LEAD STYLE ONLY)
(AVAILABLE ON POSITIONS 2-24,
2-4 POSITIONS MUST BE IN -TR)ROW SPECIFICATION
-S: SINGLE (USE FHP-XX-S)PLATING SPECIFICATION
-T: MATTE TIN CONTACT AND TAIL (USE C-130-XX-T)
-TM: MATTE TIN CONTACT AND TAIL (USE C-130-XX-T)
-H: 30μ" GOLD IN CONTACT AREA,
3μ" GOLD ON TAIL (USE C-130-XX-H)SECTION "A"- "A"
STYLE -02

NOTES:

STYLE -01

1. REPRESENTS A CRITICAL DIMENSION.
2. COPLANARITY TO BE WITHIN .006".
3. BURR ALLOWANCE: .0015 MAX.
4. MAXIMUM CUT FLASH: .020.
5. MINIMUM PUSHOUT FORCE: 1.0 LB.
6. LAYER PACKAGE STYLE -01 & -02, POSITIONS 02 - 04 WITH NO OPTIONS ONLY.
7. OPEN PART OF CONTACT FILLED TOWARDS #1 PIN INDICATOR
8. MINIMUM WALL THICKNESS TO BE .010".
9. MEASURED @ BEND.
10. TUBE PACKAGING AVAILABLE FOR 5 THRU 24 POSITIONS.
11. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
12. POLARIZATION NUMBER INDICATES THE AMOUNT OF LIVE CONTACTS IN THE CONNECTOR.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ± .01
.XXX: ± .005
.XXXX: ± .0020

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1.5:1
MATERIAL: VECTRA E130i
COLOR: BLACK
CONTACT: BeCu, 174HT


F:\dwg\sw\exisprod\assembly\156\FHP-XX-XX-XX-S-XX-XX-A5M.slddrw

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322DESCRIPTION:
.156 HI POWER SOCKET ASSEMBLY



DWG. NO. FHP-XX-XX-XX-S-XX-XX-XX

BY: BRATCHER 03/01/99 SHEET 1 OF 3





NOTE: "M" = USED MEASURED DIMENSION (REF)
"P" = $\{["M" - .256 [6.50]] / 2\} \pm .020 [.51]$

FIG 3
-K: POLYIMIDE FILM PAD OPTION
(SHOWN: FHP-10-02-X-S-K)



(TUBE PACKAGING AVAILABLE FOR 5 THRU 24 POS)
(TUBE PACKAGE THE PARTS WITH #1 PIN TOWARDS ARROW)


PACKAGING TABLE			
LEAD STYLE	OPTIONS	PACKAGING TUBE	PLUG
-01	ALL OPTIONS	PT-1-24-02-44	TP-03
-02	ALL OPTIONS	PT-1-24-02-44	TP-03




F:\dwg\sw\exisprod\assembly\156\FHP-XX-XX-XX-S-XX-XX-ASM.slddrw

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING SHEET SCALE: 1:0.666667	 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322	
	DESCRIPTION: .156 HI POWER SOCKET ASSEMBLY	
	DWG. NO. FHP-XX-XX-XX-S-XX-XX-XX	
	BY: BRATCHER	03/01/99


-02 POLARIZATION
 (8 FINISHED GOODS)
 FHP-24-02-XX-S-02 SHOWN




-03 POLARIZATION
 (6 FINISHED GOODS)
 FHP-24-02-XX-S-03 SHOWN




-04 POLARIZATION
 (5 FINISHED GOODS)
 FHP-24-02-XX-S-04 SHOWN



-05 POLARIZATION
 (4 FINISHED GOODS)
 FHP-24-02-XX-S-05 SHOWN




-06 POLARIZATION
 (3 FINISHED GOODS)
 FHP-24-01-XX-S-06 SHOWN




-08 POLARIZATION
 (2 FINISHED GOODS)
 FHP-24-01-XX-S-08 SHOWN



-10 POLARIZATION
 (2 FINISHED GOODS)
 FHP-24-02-XX-S-10 SHOWN




STANDARD FILL




4 POSITION SHOWN
 [PRIOR TO CUT-TO-POSITION OPERATION]


-12 POLARIZATION
 (1 FINISHED GOODS)
 FHP-24-02-XX-S-12 SHOWN



-13 POLARIZATION
 (1 FINISHED GOODS)
 FHP-24-01-XX-S-13 SHOWN



-14 POLARIZATION
 (1 FINISHED GOODS)
 FHP-24-01-XX-S-14 SHOWN



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC, INC. AND SHALL NOT BE REPRODUCED
 OR TRANSFERRED TO OTHER DOCUMENTS OR
 DISCLOSED TO OTHERS OR USED FOR ANY
 PURPOSE OTHER THAN THAT WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED WRITTEN
 CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.25:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

.156 HI POWER SOCKET ASSEMBLY

DWG. NO.

FHP-XX-XX-XX-S-XX-XX-XX

BY: BRATCHER

03/01/99

SHEET 3 OF 3