


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			D	REVISED PER ECO-14-015277	26FEB2015	NK DR



- 1 FOR 3.81[.150] TO 6.35[.250] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK 1.22 ± 0.05 [.048 $\pm$.002]
- 3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

1	WIRE TERMINAL	BODY: COPPER ASTM-B152 TIN PL ASTM-B545 SLEEVE: COPPER ASTM-B152 INSULATION: YELLOW NYLON	36203
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.20 [.008]
4 PLC ± -
ANGLES ± .5°
FINISH -

DWN RAGHAVEDRA 12JUN09
CHK JEFF RUTH 12JUN09
APVD TOM MICHIELUTTI 12JUN09

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
WIRE TERMINAL PIDG - RING TONGUE
WIRE SIZE: 16-14 HD

SIZE A3
CAGE CODE 00779
DRAWING NO C-36203
SCALE 2:1

RESTRICTED TO
-
SHEET 1 OF 1
REV D