

		REVISIONS																																																																																		
		REV	DESCRIPTION	DATE	APPROVED																																																																															
		01 ₀	RELEASED	KYLE 10/22/97	PCW																																																																															
B	REVISED PER ECN 0U20-0262-01	GV 1/6/03	JGH																																																																																	
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A</td><td>TEMPERATURE RATING -65° TO +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>Fig. 321-1</td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 335</td><td>Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR 1.07+0.01f(GHz) DC to 18 GHz</td><td>Center Contact Captivation</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B</td></tr><tr><td>Insertion Loss (dB MAX) .03x√f(GHz)</td><td>Axial (Lbs) 6.0</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))</td><td>Weight (Grams) TBD</td><td>Corrosion - MIL-STD-202, Method 101, Condition B</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td></td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000</td><td></td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 10000</td><td></td><td></td></tr></table>		ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A	TEMPERATURE RATING -65° TO +125°C	Frequency Range (GHz) DC to 18	Fig. 321-1	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level 335	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Shock MIL-STD-202, Method 213, Condition I	VSWR 1.07+0.01f(GHz) DC to 18 GHz	Center Contact Captivation	Thermal Shock MIL-STD-202, Method 107, Condition B	Insertion Loss (dB MAX) .03x√f(GHz)	Axial (Lbs) 6.0	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))	Weight (Grams) TBD	Corrosion - MIL-STD-202, Method 101, Condition B	Corona, 70,000 Ft (VRMS MIN) 250			Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000			Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670			I.R.(Megohms MIN) 10000			<table><tr><td>HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>O-RING</td><td>FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.</td><td>N/A</td></tr></table> <table><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON</td><td>FRAC. DEC. ANGLES</td><td></td></tr><tr><td>± 1/64 ± .005 ± 1°</td><td></td><td></td></tr><tr><td>These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASS'Y PROCEDURE</td><td></td></tr><tr><td></td><td>NO. A.P. N/A</td><td></td></tr></table> <table><tr><td>DRWN BY PCW</td><td>DATE 9/11/97</td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>CHECKED BY</td><td></td></tr><tr><td>APP'D BY PCW</td><td>10/2/97</td></tr><tr><td colspan="2">TITLE</td><td></td></tr><tr><td colspan="2">DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL</td><td></td></tr><tr><td>SIZE B</td><td>CODE IDENT NO. 26805</td><td>REV 01₀</td></tr><tr><td colspan="2">SCALE 4:1</td><td>SHEET 1 OF 1</td></tr></table>	HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	O-RING	FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A	COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	FRAC. DEC. ANGLES		± 1/64 ± .005 ± 1°			These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE			NO. A.P. N/A		DRWN BY PCW	DATE 9/11/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	CHECKED BY		APP'D BY PCW	10/2/97	TITLE			DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL			SIZE B	CODE IDENT NO. 26805	REV 01 ₀	SCALE 4:1		SHEET 1 OF 1
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																		
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A	TEMPERATURE RATING -65° TO +125°C																																																																																		
Frequency Range (GHz) DC to 18	Fig. 321-1	Vibration MIL-STD-202, Method 204, Condition D																																																																																		
Volt Rating (VRMS MAX) @ Sea Level 335	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Shock MIL-STD-202, Method 213, Condition I																																																																																		
VSWR 1.07+0.01f(GHz) DC to 18 GHz	Center Contact Captivation	Thermal Shock MIL-STD-202, Method 107, Condition B																																																																																		
Insertion Loss (dB MAX) .03x√f(GHz)	Axial (Lbs) 6.0	Moisture Resistance MIL-STD-202, Method 106																																																																																		
RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))	Weight (Grams) TBD	Corrosion - MIL-STD-202, Method 101, Condition B																																																																																		
Corona, 70,000 Ft (VRMS MIN) 250																																																																																				
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000																																																																																				
Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0																																																																																				
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670																																																																																				
I.R.(Megohms MIN) 10000																																																																																				
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																																																		
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																		
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																																																		
O-RING	FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A																																																																																		
COMPONENT	MATERIAL	FINISH																																																																																		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	FRAC. DEC. ANGLES																																																																																			
± 1/64 ± .005 ± 1°																																																																																				
These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE																																																																																			
	NO. A.P. N/A																																																																																			
DRWN BY PCW	DATE 9/11/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																																		
CHECKED BY																																																																																				
APP'D BY PCW	10/2/97																																																																																			
TITLE																																																																																				
DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL																																																																																				
SIZE B	CODE IDENT NO. 26805	REV 01 ₀																																																																																		
SCALE 4:1		SHEET 1 OF 1																																																																																		