



10. Hammers and striking tools

► Hammers - mallets

462



Graphite handle hammers.....	462
Hickory handle hammers.....	464
Club and sledge hammers and wooden mallets	467

► Soft-faced hammers and mallets

468



Dead-blow hammers	468
Interchangeable-tip mallets	468
Drifts	470


► Soft-faced hammers and mallets

471




3-material drift set	471
Sets of tips.....	472

► Flat chisels – cape chisels




► Sheathed impact tools

472



► Impact tools


475



Sheathed drift punches	475
Nail sets.....	476
Centre punches	476
Automatic centre punches	476

► Impact tool sets

476



478




► Graphite handle hammers

New**GRAPHITE HANDLE HAMMERS****Profiber****THE SAFE HAMMER****Maximum safety.**

- Permanent epoxy resin head-to-handle connection.
- Unbreakable.

Absolute comfort

- Anti vibration : absorbent material and narrow upper handle profile to reduce vibration.

**Positive grip.**

- Soft elastomer handle for a comfortable hold.
- Wider guard to prevent loss of grip.

A combination of 3 materials for a perfect result.**1- Graphite :**


For strength. No risk of breakage.

Polypropylene :

For reduced vibration.

Elastomer :

For a perfect grip and excellent resistance to corrosive workshop liquids.

**Safety first**

Wear eye protection.





New

200C Graphite handle "riveting" engineers hammer

- ▷ NF E 71-014, ISO 15601.
• Graphite core safety handle.

	I mm	H mm	L mm	ΔΔ kg
200C.26	80	25	245	0,345
200C.28	88	28	270	0,380
200C.30	93	30	270	0,470
200C.32	100	32	300	0,585
200C.36	106	35	300	0,725
200C.40	108	40	330	1,025
200C.42	117	42	330	1,130
200C.50	138	50	360	1,910
200C.60	151	60	380	2,800




New

205C Graphite handle "DIN" engineers hammer

- ▷ ISO 15601, DIN 1041, NF ISO 15601.
• Graphite core safety handle.

	I mm	H mm	L mm	ΔΔ kg
205C.20	96	19	280	0,250
205C.30	106	23	300	0,380
205C.50	122	27	320	0,580
205C.80	132	33	350	0,960
205C.100	137	36	360	1,140




New**WOOD HANDLE HAMMERS****SAFE, ERGONOMIC AND COMFORTABLE****Head.****"High security" triple wedge handle attachment :**

- 2 steel + 1 wooden wedge for a better distribution contact surfaces between the handle and the head.

Head very firmly secured on the handle

- Precise heat treatment of the head.

**Handle.****Hickory :**


- Excellent mechanical strength.
- Unaffected by climatic differences.

Octagonal handle profile :

- Exclusive to FACOM.
- Best compromise between mechanical strength and absorption of vibration.


**Growth ring**

Our handles are made only from blocks with a strictly defined number of growth rings as this determines the rate of growth of the tree.
Fast growth, few rings, low density wood and thus low mechanical strength.




Always inspect a hammer before use. If damaged in any way, discard it. Watch out for :

- Excessively worn or mushroomed head.
- Suspect fit.
- Scored handle.




For safety, the hammer should hit dead square in the centre of the face.

Facom hammers are quality tools. Steady precise blows will prolong tool life.



Flying chips are dangerous. never hammer materials harder than 46 HRc. Use a FACOM mallet instead.



Always choose the, correct head, of appropriate weight and size :

the FACOM range includes models for all applications.

**Safety first**

Wear eye protection




Hammers - mallets

200H Riveting hammers

▷ NF E 71-014, ISO 15601.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I	H	L		ΔΔ
	mm	mm	mm	Hickory	kg
200H.26	80	25	245	210.MHB01	0,345
200H.28	88	28	270	210.MHB02	0,380
200H.30	93	30	270	210.MHB03	0,470
200H.32	100	32	300	210.MHB04	0,585
200H.36	106	35	300	210.MHB04	0,725
200H.40	108	40	330	210.MHB05	1,025
200H.42	117	42	330	210.MHB05	1,130
200H.50	138	50	360	210.MHB06	1,910
200H.60	151	60	380	210.MHB27	2,800



Impact tool module

MOD.MI1

200H.32 Hammer.

208A.32CB Mallet.

263.20 Chisel.

256.6 Centre punch.

248. Long drift punches 4 - 5 - 6 mm.

- Complete with tray PL.333.

ΔΔ : 1.800 kg.




205H "DIN" engineers hammers

▷ ISO 15601, DIN 1041, NF ISO 15601.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I	H	L		ΔΔ
	mm	mm	mm	Hickory	kg
205H.20	96	19	280	210.MHB12	0,250
205H.30	106	23	300	210.MHB13	0,380
205H.50	122	27	320	210.MHB14	0,580
205H.80	132	33	350	210.MHB15	0,960
205H.100	137	36	360	210.MHB16	1,140



Impact tool module 205

MOD.MI3

- Comprising :

- 205H.50 Hammer.

- 208A.32CB Mallet.

- 263.18 Chisel.

- 256.6 Centre punch.

- 248. Long drift punches 4 - 5 - 6 mm.

- Tray PL.333.

ΔΔ : 1.705 kg.




202H Ball pein engineers hammers

▷ ISO 15601.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I	Ø	L		ΔΔ
	mm	mm	mm	Hickory	kg
202H.1/4	65	20	275	210.MHB07	0,140
202H.1/2	84	26	297	210.MHB08	0,280
202H.1	104	31	322	210.MHB09	0,430
202H.1'1/2	123	37	363	210.MHB10	0,840
202H.2	128	40	394	210.MHB11	1,110



Impact tool module 202

MOD.MI4PB

202H.1/2 Hammer.

208A.32CB Mallet.

263.18 Chisel.

256.6 Centre punch.

248. Long drift punches 4 - 5 - 6 mm.


• Complete with tray PL.333.

 $\Delta\Delta$: 1.45 kg.**860H Round face dinging hammers**

▷ ISO 15601, NF ISO 15601.

• Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	l mm	Ø mm	L mm	 Hickory	$\Delta\Delta$ kg
860H.22	104	22	280	210.MHB25	0,180
860H.26	114	26	297	210.MHB26	0,340
860H.28	118	28	297	210.MHB26	0,370
860H.30	123	30	314	210.MHB28	0,440
860H.32	134	32	339	210.MHB29	0,570
860H.36	139	36	339	210.MHB29	0,700
860H.40	149	40	377	210.MHB31	0,920


**Square face dinging hammer****859A.28**

▷ ISO 15601.

• Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

 $\Delta\Delta$: 560 g.


	Handles	l mm	H mm	L mm	$\Delta\Delta$ kg
859H.28	210.MHB34	140	28	319	0,560

**213H Welders chipping hammers**

▷ ISO 15601, DIN 6465, NF ISO 15601.

• Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	l mm	H mm	L mm	 Hickory	$\Delta\Delta$ kg
213H.30	170	21	270	210.MHB32	0,340
213H.40	180	21	270	210.MHB32	0,480




Hammers - mallets

203H Electricians hammer

▷ ISO 15601, NF E 71-011.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I mm	H mm	L mm	 Hickory	ΔΔ kg
203H.16	141	16	237	210.MHB17	0,160
203H.18	142	18	237	210.MHB18	0,200




215H Joiners hammers

▷ ISO 15601, NF E 71-012.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I mm	H mm	L mm	 Hickory	ΔΔ kg
215H.20	91	20	264	210.MHB19	0,210
215H.22	99	22	283	210.MHB20	0,270
215H.26	109	26	285	210.MHB21	0,360




Claw hammer

204

- Permanent tubular handle, Neoprene grip.
- Balanced head with nail claw.
- Polished chrome finish.

ΔΔ : 800 g.




Club and sledge hammers and wood mallets

1262H Bevelled edge club hammers

▷ ISO 15601, DIN 6475, NF ISO 15601.

- Hickory handle, "high security" triple wedge design (1 wooden and 2 metal wedges).

	I mm	H mm	L mm	 Hickory	ΔΔ kg
1262H.100	100	40	245	210.MHB22	1,000
1262H.125	105	43	248	210.MHB23	1,250
1262H.150	115	45	254	210.MHB24	1,500



Sledge hammer

1263A.400

▷ ISO 15601, DIN 6475, NF ISO 15601.

- "High security" hickory handle.

	Handles	l mm	H mm	L mm	ΔΔ kg
1263H.400	210.MHB35	175	60	880	4,800
	Description				
210.MH45	Spare sledge hammer handle				




209 Wood mallets

▷ DIN 7462.

- Compressed laminated wood.
- Inset glass-fibre bands.
- Hornbeam handle.

	Ø mm	L mm	l mm	ΔΔ g
209.50	50	290	100	320
209.60	60	320	120	500
209.70	70	360	140	760



Soft face hammers

▶ Dead-blow hammers





Dead-blow hammers

SAFE, ERGONOMIC AND COMFORTABLE

Deadening the blow

- The head is half-filled with steel balls, the mass of which has sufficient inertia to counteract any tendency to bounce back. After striking, the face of the hammer remains in position, without the damaging effects of rebound when Hammering home an accurate fit. The nylon or polyurethane striking faces remove the risk of lying chips when hitting hard metal objects. Steel body and handle.

**"Monobloc" polyurethane hammer**


- In addition to the dead-blow feature the soft-face hammer 216 is fully moulded in a polyurethane shell.
- This monobloc design protects the head from splitting and the balls escaping in the workshop.
- The chemical-resistant polyurethane moulding gives the tips a far longer service life than conventional soft-faced hammers.

Soft face hammers

216 Dead-blow hammers, monobloc

- Steel-ball dead-blow design.
- Polyurethane encapsulated steel body and handle.
- Shore hardness D63 on striking faces.
- Ergonomic PVC grip.

	Ø	L	l	ΔΔ
	mm	mm	mm	kg
216.40	40	298	110	0,72
216.50	50	308	115	0,95
216.60	60	315	120	1,4



212A Dead-blow hammers, interchangeable tips

- Glass-fibre handle.
- Steel body.
- Easily replaceable, special nylon tips. Shore hardness D74.
- Ergonomic ribbed PVC grip.
- Stove-enamel hammer finish.

	L	l	Ø	Bits	ΔΔ
	mm	mm	mm		kg
212A.35	305	112	35	212.E35	0,69
212A.40	310	117	40	212.E40	0,76
212A.50	320	120	50	212.E50	1,07
212A.60	330	138	60	212.E60	1,68



► Interchangeable-tip mallets

207A - 208A Adaptable-tip mallets

207A : Lightweight-series, aluminium body.

208A : Heavyweight-series, brass body.

- Mallets are available with a limited number of tip combinations only, but you can customize your mallet by selecting a body and two tips of your choice.

	Lightweight/Heavyweight	Ø	Bits	ΔΔ
		mm		kg
207A.25CB	Lightweight-series	25	EC - EB	0,135
207A.32CB	Lightweight-series	32	EC - EB	0,205
207A.40CB	Lightweight-series	40	EC - EB	0,350
207A.50CB	Lightweight-series	50	EC - EB	0,350
207A.60CB	Lightweight-series	60	EC - EB	0,528
208A.25CB	Heavyweight-series	25	EC - EB	0,220
208A.32CB	Heavyweight-series	32	EC - EB	0,345
208A.32AB	Heavyweight-series	32	EA - EB	0,390
208A.32BB	Heavyweight-series	32	EB - EB	0,375
208A.40CB	Heavyweight-series	40	EC - EB	0,615
208A.40CC	Heavyweight-series	40	EC - EC	0,626
208A.50CB	Heavyweight-series	50	EC - EB	1,050
208A.60CB	Heavyweight-series	60	EC - EB	1,663

207A - 208A Mallet bodies

207A : Lightweight aluminium body, hickory handle.

208A : Heavyweight brass body, hickory handle.

	Lightweight/Heavyweight	Length	Ø	Hickory	ΔΔ
		mm	mm		kg
207A.25	Lightweight-series	280	25	210.MH12	0,135
207A.32	Lightweight-series	300	32	210.MH13	0,195
207A.40	Lightweight-series	323	40	210.MH14	0,270
207A.50	Lightweight-series	350	50	210.MH15	0,410
207A.60	Lightweight-series	363	60	210.MH16	0,610
208A.25	Heavyweight-series	280	25	210.MH12	0,235
208A.32	Heavyweight-series	300	32	210.MH13	0,340
208A.40	Heavyweight-series	323	40	210.MH14	0,525
208A.50	Heavyweight-series	350	50	210.MH15	0,830
208A.60	Heavyweight-series	363	60	210.MH16	1,260

