

Detailed Specifications & Technical Data

BELDEN
SENDING ALL THE RIGHT SIGNALS

ENGLISH MEASUREMENT VERSION

7935A Multi-Conductor - Category 5e Low Smoke Zero Halogen



For more Information
please call

1-800-Belden1



General Description:

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, sunlight - resistant LSZH jacket, rip cord. Sequential marking at two foot intervals.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
4	24	Solid	BC - Bare Copper	.020

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PO - Polyolefin	.009	.035

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
LSZH - Low Smoke Zero Halogen

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.230 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -10°C To +75°C

Installation Temperature Range: +5°C To +75°C

Operating Temperature Range: -10°C To +75°C

Bulk Cable Weight: 19 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius/Minor Axis: 0.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (RoHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 08/30/2006

EU Directive 2002/96/EC (WEEE): Yes

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

7935A Multi-Conductor - Category 5e Low Smoke Zero Halogen

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL verified to Category 5e, Ethernet/IP™ Compliant
Applicable Patents:	

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1581 Vertical Tray, UL1685 Vertical Tray Flame Test
CSA Flame Test:	FT1

Suitability

Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
510

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	63.3	63.3	20.0
4	4.0	56.3	56.3	52.3	52.3	23.6
8	5.7	51.8	51.8	46.1	46.1	25.4
10	6.4	50.3	50.3	43.9	43.9	26.0
16	8.1	47.3	47.3	39.1	39.1	26.0
20	9.2	45.8	45.8	35.2	35.2	26.0
25	10.3	44.3	44.3	34.1	34.1	25.5
31.25	11.6	42.9	42.9	31.3	31.3	25.0
62.5	16.8	38.4	38.4	21.6	21.6	23.5
100	21.7	35.3	35.3	17.1	17.1	22.5
155	27.7	32.5	32.5	4.7	4.7	19.0
200	32.0	30.8	30.8	3.0	3.0	19.0
250	36.4	29.3	29.3	>0	>0	18.0
300	40.5	28.2	28.2	>0	>0	18.0
310	41.3	27.9	27.9			18.0
350	44.3	27.2	27.2			17.0

Premise Cable Electrical Table 2:

7935A Multi-Conductor - Category 5e Low Smoke Zero Halogen

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	95-110	63.8	60.8
4	100 ± 12	95-110	51.7	48.7
8	100 ± 12	95-107	45.7	42.7
10	100 ± 12	95-107	43.8	40.8
16	100 ± 12	95-107	39.7	36.7
20	100 ± 12	95-107	37.7	34.7
25	100 ± 15	95-107	35.8	32.8
31.25	100 ± 15	95-107	33.9	30.9
62.5	100 ± 15	95-107	27.8	24.8
100	100 ± 15	95-107	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: EtherNet IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7935A 0101000	1,000 FT	30.000 LB	BLACK	C	4 PR #24 PP FRNHPO
7935A 0102000	2,000 FT	58.000 LB	BLACK	C	4 PR #24 PP FRNHPO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 03-11-2014

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7935A 0101000](#) [7935A 0102000](#)