



NTC Thermistors, Surface Mount Chip



FEATURES

- Top and bottom surface terminations
- High-density monolithic ceramic construction
- Allows design flexibility for use with hybrid circuitry
- Model W is a thermistor die with silver conductors fired on the top and bottom surfaces. The bottom surface can be reflow soldered or conductive epoxied directly to a substrate bonding pad and the top surface wire bonded to complete the circuit connection.

STANDARD ELECTRICAL SPECIFICATIONS AND DIMENSIONS in inches [millimeters]



R25 (Ω)	PART NUMBER	CURVE NUMBER	L	W	T (nominal)
10.0M	12W1004	12	0.043 $\pm$ 0.004 [10.1 $\pm$ 0.10]	0.043 $\pm$ 0.004 [10.1 $\pm$ 0.10]	0.020 [0.51]
500 000	12W5003	12	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.016 [0.41]
250 000	12W2503	12	0.075 $\pm$ 0.006 [10.9 $\pm$ 0.15]	0.075 $\pm$ 0.006 [10.9 $\pm$ 0.15]	0.016 [0.41]
200 000	7W2003	7	0.041 $\pm$ 0.004 [10.0 $\pm$ 0.10]	0.041 $\pm$ 0.004 [10.0 $\pm$ 0.10]	0.033 [0.84]
100 000	12W1003	12	0.119 $\pm$ 0.008 [30.0 $\pm$ 0.20]	0.119 $\pm$ 0.008 [30.0 $\pm$ 0.20]	0.016 [0.41]
100 000	8W1003	8	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.029 [0.74]
100 000	7W1003	7	0.054 $\pm$ 0.005 [10.4 $\pm$ 0.13]	0.054 $\pm$ 0.005 [10.4 $\pm$ 0.13]	0.029 [0.74]
80 000	8W8002	8	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.024 [0.61]
50 000	8W5002	8	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.018 [0.46]
50 000	7W5002	7	0.051 $\pm$ 0.004 [10.3 $\pm$ 0.10]	0.051 $\pm$ 0.004 [10.3 $\pm$ 0.10]	0.014 [0.36]
30 000	8W3002	8	0.072 $\pm$ 0.005 [10.8 $\pm$ 0.13]	0.054 $\pm$ 0.005 [10.4 $\pm$ 0.13]	0.015 [0.38]
30 000	7W3002	7	0.069 $\pm$ 0.005 [10.8 $\pm$ 0.13]	0.069 $\pm$ 0.005 [10.8 $\pm$ 0.13]	0.015 [0.38]
30 000	1W3002	1	0.029 $\pm$ 0.003 [0.74 $\pm$ 0.08]	0.029 $\pm$ 0.003 [0.74 $\pm$ 0.08]	0.032 [0.81]
20 000	1W2002	1	0.035 $\pm$ 0.004 [0.89 $\pm$ 0.10]	0.035 $\pm$ 0.004 [0.89 $\pm$ 0.10]	0.032 [0.81]
15 000	1W1502	1	0.041 $\pm$ 0.004 [10.0 $\pm$ 0.10]	0.041 $\pm$ 0.004 [10.0 $\pm$ 0.10]	0.032 [0.81]
10 000	1W1002	1	0.050 $\pm$ 0.005 [10.3 $\pm$ 0.13]	0.050 $\pm$ 0.005 [10.3 $\pm$ 0.13]	0.032 [0.81]
3000	1W3001	1	0.068 $\pm$ 0.005 [10.7 $\pm$ 0.13]	0.054 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.015 [0.38]
2000	1W2001	1	0.101 $\pm$ 0.006 [20.6 $\pm$ 0.15]	0.054 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.015 [0.38]
2000	2W2001	2	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.049 $\pm$ 0.004 [10.2 $\pm$ 0.10]	0.037 [0.94]
1000	2W1001	2	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.053 $\pm$ 0.004 [10.4 $\pm$ 0.10]	0.022 [0.56]
1000	1W1001	1	0.105 $\pm$ 0.006 [20.7 $\pm$ 0.15]	0.105 $\pm$ 0.006 [20.7 $\pm$ 0.15]	0.015 [0.38]
500	2W5000	2	0.060 $\pm$ 0.005 [10.5 $\pm$ 0.13]	0.060 $\pm$ 0.005 [10.5 $\pm$ 0.13]	0.015 [0.38]
500	1W5000	1	0.148 $\pm$ 0.006 [30.8 $\pm$ 0.15]	0.148 $\pm$ 0.006 [30.8 $\pm$ 0.15]	0.015 [0.38]
300	2W3000	2	0.077 $\pm$ 0.006 [20.0 $\pm$ 0.15]	0.077 $\pm$ 0.006 [20.0 $\pm$ 0.15]	0.015 [0.38]
50	2W0500	2	0.188 $\pm$ 0.012 [40.8 $\pm$ 0.31]	0.188 $\pm$ 0.012 [40.8 $\pm$ 0.31]	0.015 [0.38]

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: 08W8002KT (preferred part number format)

0 8 W 1 0 0 2 K T

CURVE	GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING
01 02 07 08 12	W	1002 = 10K	J = $\pm$ 5 % K = $\pm$ 10 %	E = Lead (Pb)-free, Tray T = Tin/Lead, Tray

Historical Part Number example: TOMC16011002Z (will continue to be accepted)

08	W	8002	K	T
HISTORICAL CURVE	GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[01W3002KP](#) [08W8002JP](#) [07W5002JP](#) [08W5002JP](#) [07W1003KP](#) [08W1003KP](#) [01W1002KP](#) [01W1002JP](#) [2W5000](#)
[02W5000KP](#) [02W1001JP](#) [01W5001JP](#) [1W1001-10](#) [01W2002JP](#) [07W3002JP](#) [02W1000JP](#) [02W1000KP](#)
[02W5000JP](#) [01W2001JP](#)