




ACCESSORIES

(NOT PART OF STANDARD ASSEMBLY)
SEE DRAWING 10-150000

REVISIONS

LTR	DESCRIPTION	DATE	APPVD
A	INITIAL RELEASE NUM: -----		
B	(CL 11) SEE ECN: 97133	02/12/07	J. BIANCHI
C	(CL 11) SEE ECN A3037	7-13-07	N.VANDEWEERT



SEE SHEET 2.

NOTES:
WARNING: IF THIS BOX ☐ IS CHECKED: THIS DRAWING HAS BEEN MODIFIED BY HAND-DRAFTING WITHOUT COMPUTER UPDATING

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.


N/A
N/A

NEXT ASSEMBLY

PRO/ENGINEER INFORMATION

Pro/e Model Used:
58-627851-18.ASSEM
Drawing Name:
58-533720-29

THIRD ANGLE PROJECTION



TEST
9-3353-1
ASSY
9-3605-1,9-2811
9-2437-1

6	I	10-330914-XXI	GASKET	
5		SEE NOTE 7	CONTACTS	
4	I	10-101806/824-()P OR 10-252806/824-()P OR 10-101806/824-()S OR 10-252806/824-()S	INSERT, PIN INSERT, PIN INSERT, SOCKET INSERT, SOCKET	
3	I	10-123017-XXX	NUT	
2	I	SEE COLUMN	PACKING	
1	I	10-150903-XXX	SHELL	
POS	QTY	PART NUMBER	DESCRIPTION	NOTE

PARTS LIST

APPROVALS	DATE
PREPARED J. BORDEAU	04-Mar-02
CHECKED-ENG	
APPROVED-MATERIAL LAB	
APPROVED-PROCESS	
APPROVED-ENG-IN-CHG	
APPROVED-QUALITY	
APPROVED-ENG MGR	

AMPHENOL CORPORATION AMPHENOL AEROSPACE OPERATIONS STONEY, N.Y. 13838			
CONNECTOR, ELECTRICAL, RECEPTACLE, TYPE PT-C() JFB, CONDUCTIVE BLACK ZINC COBALT			
SIZE C	FSCM NO. 77820	DOCUMENT NO. 58-533720/729	REV. C
SCALE: 2.0	REF: 71-533720/729	SHEET 1 OF 2	

ASSEMBLY NUMBER	PT NUMBER REF	DETAIL	DIMENSIONS														
		PACKING	C +.010 -.025	D +.010 -.025	E +.010 -.020	G PANEL THK		K +.011 -.010	M	ØN +.001 -.005	P HEX +.017 -.016	S	U MAX	Z +.025 -.035	RR	ØSS +.000 -.016	ZZ +.000 -.010
						MIN	MAX								THREAD (PLATED)		
															SIZE CLASS 2A		
58-533720-()	07C-06-() (027)	10-90351-15	.337	.025	.085	.062	.125	.125	.696	.348	.625	.812	.153	.376	.4375-28 UNEF	.439	.405
58-533721-()	07C-08-() (027)	10-90351-17								.473	.750	.938			.5625-24 UNEF	.563	.530
58-533722-()	07C-10-() (027)	10-90351-19								.590	.875	1.062			.6875-24 UNEF	.680	.655
58-533723-()	07C-12-() (027)	10-90351-22								.750	1.062	1.250			.8750-20 UNEF	.859	.818
58-533724-()	07C-14-() (027)	10-90351-24								.875	1.188	1.375			1.0000-20 UNEF	.984	.942
58-533725-()	07C-16-() (027)	10-90351-26								1.000	1.312	1.500			1.1250-18 UNEF	1.108	1.066
58-533726-()	07C-18-() (027)	10-90351-28								1.125	1.438	1.625			1.2500-18 UNEF	1.233	1.191
58-533727-()	07C-20-() (027)	10-90351-128	.399	.087	.147	.250	.156	.884	.917	1.250	1.562	1.812	.215	.367	1.3750-18 UNEF	1.358	1.316
58-533728-()	07C-22-() (027)	10-90351-130								1.375	1.688	1.938			1.5000-18 UNEF	1.483	1.441
58-533729-()	07C-24-() (027)	10-90351-132								1.500	1.812	2.062		1.6250-18 UNEF	1.610	1.566	

9. UNITS ILLUSTRATED MEET THE APPLICABLE REQUIREMENTS OF MIL-C-26482.
8. FOR MAXIMUM SEALING EFFICIENCY, APPLY A LIGHT COAT OF COMPOUND (MIL-S-8660) TO PACKING.
7. SEE SEPARATE PARTS LIST FOR COMPONENT PART NUMBERS AND QUANTITIES.
6. SEE DRAWING 58-146606 THRU 58-146650 AND OTHERS FOR REQUIRED MATING PLUG ASSEMBLY.
5. INSERTS AND CONTACTS MUST NOT BE REMOVED.
4. SEE WORK ORDER FOR PERMISSIBLE ADDITIONAL OR ALTERNATE STAMPING.
3. DISTANCE BETWEEN END OF SHELL AND THE POINT AT WHICH A GAGE PIN, HAVING THE SAME BASIC DIAMETER AS THE MATING CONTACT AND A SQUARE FACE, ENGAGES SOCKET CONTACT SPRING.
2. TO COMPLETE ASSEMBLY NUMBER AND PT NUMBER REF, ADD APPLICABLE INSERT ARRANGEMENT SUFFIX TO BASE NUMBERS LISTED ABOVE PER 9-2437-1.
1. FOR CONTACT ARRANGEMENTS SEE DRAWINGS L-15206-() THRU L-15250-().

NOTES:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORPORATION.

SIZE	FSCM NO.	DOCUMENT NO.	REV.
C	77820	58-533720/729	C
SCALE: 1:5		REF: 71-533720/729	SHEET 2 OF 2