



4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Features :

- High radiant intensity
- Peak wavelength $\lambda_p=940\text{nm}$
- View angle 25°
- High reliability
- 2.54mm Lead spacing

■ Description :

- EVERLIGHT's Infrared Emitting Diode (IR313) is a high intensity diode, molded in a blue transparent plastic package.

The device is spectrally matched with phototransistor, photodiode and infrared receiver module.

■ Applications :

- Free air transmission system
- Optoelectronic switch
- Floppy disk drive
- Infrared applied system
- Smoke detector


PART NO.	CHIP	LENS COLOR
	MATERIAL	
IR	GaAlAs	Blue



4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Package Dimensions :



■ Notes :

1. All dimensions are in millimeter.
2. Protruded resin under flange 1.5 mm Max.
3. Lead spacing is measured where the lead emerge from the package.
4. Lens color : Blue transparent.
5. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
6. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
7. When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.



4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Absolute Maximum Ratings at $T_A = 25^{\circ}\text{C}$

Parameter	Symbol	Rating	Unit	Notice
Continuous Forward Current	I_F	100	mA	
Peak Forward Current Pulse width=100 μs , Duty cycle=1%	I_{FP}	1.0	A	
Reverse Voltage	V_R	5	V	
Operating Temperature	T_{opr}	-40 ~ +85	$^{\circ}\text{C}$	
Storage Temperature	T_{stg}	-40 ~ +85	$^{\circ}\text{C}$	
Soldering Temperature	T_{sol}	260	$^{\circ}\text{C}$	4mm from mold body less than 5 seconds
Power Dissipation at(or below) 25 $^{\circ}\text{C}$ Free Air Temperature	P_d	150	mW	

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Radiant Intensity	E_e	7.8	15	----	mW/sr	$I_F=20\text{mA}$
		----	75	----		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	700	----		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Peak Wavelength	λ_p	----	940	----	nm	$I_F=20\text{mA}$
Spectral Bandwidth	$\Delta \lambda$	----	45	----	nm	$I_F=20\text{mA}$
Forward Voltage	V_F	----	1.2	1.5	V	$I_F=20\text{mA}$
		----	1.4	1.8		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	2.6	4.0		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Reverse Current	I_R	----	----	10	μA	$V_R=5\text{V}$
View Angle	$2\theta_{1/2}$	----	25	----	deg	$I_F=20\text{mA}$



4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Typical Electrical/Optical/Characteristics Curves

Fig. 1 Forward Current vs. Ambient Temperature




Fig. 2 Spectral Distribution




Fig. 3 Peak Emission Wavelength vs. Ambient Temperature





Fig. 4 Forward Current vs. Forward Voltage





4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Typical Electrical/Optical/Characteristics Curves

Fig. 5 Relative Intensity vs.
Forward Current




Fig. 6 Relative Radiant Intensity vs.
Angular Displacement




Fig. 7 Relative Intensity vs.
Ambient Temperature ($^{\circ}\text{C}$)





Fig. 8 Forward Current vs.
Ambient Temperature ($^{\circ}\text{C}$)





EVERLIGHT ELECTRONICS CO., LTD.

DEVICE NUMBER : DIR-031-191
ECN : _____

REV : 1.0
PAGE : 6/8

4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level:90%

LTPD:10%

NO.	Item	Test Conditions	Test Hours/ Cycles	Sample Sizes	Failure Judgement Criteria	Ac/Re
1	Solder Heat	TEMP : 260℃ ± 5 ℃	5 secs	22 pcs	$I_R \geq U \times 2$ $E_e \leq L \times 0.8$ $V_F \geq U \times 1.2$ U :Upper specification limit L :Lower specification limit	0/1
2	Temperature Cycle	H : +85℃ 30 mins ↑ 5 mins ↓ L : -55℃ 30 mins	50 cycles	22 pcs		0/1
3	Thermal Shock	H : +100℃ 5 mins ↑ 10 secs ↓ L : -10℃ 5 mins	50 cycles	22 pcs		0/1
4	High Temperature Storage	TEMP. : +100℃	1000 hrs	22 pcs		0/1
5	Low Temperature Storage	TEMP. : -55℃	1000 hrs	22 pcs		0/1
6	DC Operating Life	$I_F = 20\text{mA}$	1000 hrs	22 pcs		0/1
7	High Temperature / High Humidity	85℃ / 85% R.H.	1000 hrs	22 pcs		0/1



DEVICE NUMBER : DIR-031-191
ECN :

REV : 1.0
PAGE : 7/8

4.7mm Round Non-Flange Infrared LED


MODEL NO : IR313

■ Test Method For Power :

Condition : $I_F=20\text{ mA}$

Test Item : Radiant Intensity

Unit : mW/sr



■ To Distinguish Intensity:

Condition: $I_F=20\text{mA}$

Unit : mW/sr

Bin Number	M	N	P	Q
Min	7.8	11.0	15.0	21.0
Max	12.5	17.6	24.0	34.0




DEVICE NUMBER : DIR-031-191
ECN : _____

REV : 1.0
PAGE : 8/8

4.7mm Round Non-Flange Infrared LED

MODEL NO : IR313

■ Packing Specifications



■ Packing Quantity Specification

- 500 Pcs/1Bag , 6 Bags/1Box
- 10 Boxes/1Carton