

CATALOG LISTING
US SERIES CHART 2

ISSUE
4

REVISIONS
A C094774
TSM
2AUG99
B 0098235
SBH
20FEB13

CHECK
20FEB13

CMH

CHECK

PTC/CAD 2D
DRAWN
TSM 29 JUL 99

US SERIES
CHT 2

REPLACES

RELEASE NO. CO-78499

PAGE 1 OF 1

CHECK

CHECK

CHECK


CHECK

CHECK


CHECK

CHECK



CHECK




- NOTES
- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\varnothing 1.40$ MAX ON $3.99 \pm 0.05 / .157 \pm .002$ CENTERS
 - TERMINALS ARE PLATED FOR SOLDERING
 - SWITCH WILL WITHSTAND A TEMPERATURE OF $82.2^\circ \text{C} / 180^\circ \text{F}$



OBSOLETE



SIMULATED ROLLER LEVER
SCALE 4:1



FLAT LEVER
SCALE 4:1

CONTACT TYPE	ACTUATOR TYPE	CAT. LISTING	SOLDER TERMINAL CHARACTERISTICS						
			OPERATING FORCE MAX	RELEASE FORCE MIN	PRE-TRAVEL MAX	DIFFERENTIAL TRAVEL MAX	OVER-TRAVEL MIN	OPERATING POSITION	FREE POSITION MAX
			grams OUNCES	grams OUNCES	mm INCHES	mm INCHES	mm INCHES	mm INCHES	mm INCHES
SILVER	PIN PLUNGER	(A)	100 3.527	10 .353	0.3 .012	0.1 .004	0.1 .004	5.40 ± 0.15 .213 ± .006	5.80 .228
	FLAT LEVER	(A)	25 .862	2.0 .035	2.4 .094	0.7 .028	0.4 .016	6.40 ± 0.60 .252 ± .024	9.00 .354
	SIM ROLLER LEVER	US20D10E00	30 1.058	2.0 .035	2.2 .087	0.7 .028	0.3 .012	6.70 ± 0.50 .264 ± .020	9.40 .370
GOLD	PIN PLUNGER	(A)	100 3.527	10 .353	0.3 .012	0.1 .004	0.1 .004	5.40 ± 0.15 .213 ± .006	5.80 .228
	FLAT LEVER	US10D10C00	25 .862	2.0 .035	2.4 .094	0.7 .028	0.4 .016	6.40 ± 0.60 .252 ± .024	9.00 .354
	SIM ROLLER LEVER	US10D10E00	30 1.058	2.0 .035	2.2 .087	0.7 .028	0.3 .012	6.70 ± 0.50 .264 ± .020	9.40 .370

THIRD ANGLE PROJECTION

SCALE 6 : 1

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :

	DIM.	TOL.	DIM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/.04	X.X	0.8/.03
ONE PLACE	X.X	0.4/.016	X.XX	0.38/.015
TWO PLACES	X.XX	0.15/.006	X.XXX	0.13/.005
THREE PLACES				
ANGLES				

DESIGN UNITS SI METRIC US CUSTOMARY

WEIGHT