





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2014
© COPYRIGHT 2014	BY -	ALL RIGHTS RESERVED.

COLOR CODE STRIP ALLOCATO
IN QUESTA AREA DEL COVER

(COLOR CODE STRIP)
(LOCATED ON THE COVER AS SHOWN)


VISTE SOLO PER RIFERIMENTO
VIEWS ONLY FOR REFERENCE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D20	ECR-23-186674	14SEP2023	SP	FL
	D21	REVISED PER ECR-24-197011	23FEB2024	MV	FL
	D22	ECR-24-201992	27MAR2024	TL	FL
	D23	ECN-24-281324	26AUG2024	TL	FL



- 1 NUMERI DI IDENTIFICAZIONE CAVITA'.
- (CIRCUIT IDENTIFICATION)
- 2 MARCHIO DI FABBRICA (LIBERA POSIZIONE).
- (AMP LOGO FREE POSITION)
- L'AGGANCIO PER LINGUETTA E' POSIZIONATO SOLO NELLA CAVITA' No.1 ED E' RICHIESTA SOLO SUI CONNETTORI A 2 E 3 POSIZIONI
- (RETENTION TOOTH IS REQUESTED FOR THE 2 AND 3 POS. ONLY; IT IS LOCATED ON THE CAVITY No.1 ONLY)
- 4 GEOMETRIA ALTERNATIVA DEL DENTINO DI AGGANCIO. VEDI NOTA 3 PER ALTRI DETTAGLI
- ALTERNATIVE SHAPE FOR RETENTION THOOTH. SEE NOTE 3 FOR ADDITIONAL DETAILS.
- 5 PER QUESTI P-N LA POLARIZZAZIONE POSTERIORE DEVE INTENDERSI COMPLETA, A FINE BLOCCETTO.
- (per la rappresentazione vedere foglio 1/2)
- (FOR THE INDICATE P.N'S THE POLARIZATION MUST BE AT THE END OF CONNECTOR)(see sheet 1 of 2).
- 6 - PART NUMBER NON IN PRODUZIONE
- (P/N. NOT YET RELEASED FOR PRODUCTION)
- 7 DIVENTA 6.5 PER LA CAVITA' N.RO 1 SOLO SUI CONNETTORI A 2,3 VIE.
- (BECOMES 6.5. FOR THE CAVITY NR.1 ON THE 2,3 POS. ONLY.)

- 9) PRODOTTO IDONEO SINO A 7A MAX, IN ACCORDO ALLA SPECIFICA DI PRODOTTO 108-20215
PRODUCT SUITABLE UP TO 7A MAX, ACCORDING TO PRODUCT SPEC. 108-20215
- 10) STATO DI FORNITURA: CONFEZIONAMENTO IN "VASSOI + SCATOLA" (PACKAGING: " ON TRAY PLUS CARTON BOX" 



- 11 CONFEZIONAMENTO 1:N BOBINA OBSOLETO
(PACKAGING: "ON REEL" OBSOLETED)

12 OBSOLETE PARTS: OBSOLETE STREAMLINING PER D. RENAUD/ D. SINISI

13 PRELIMINARY

14 OBSOLETE

15 SPECIAL VERSION WITH WIRE RETENTION HOOK ON COVER, DETAILS
SEE SHEET 3. SPECIAL MODIFICATION IS A MUST FOR TERMINATION
TO FIT THE HOOK DESIGN.

16 MATERIAL:PA GF; COLOR: NATURAL;
COMPLIANT TO UL-V0 GWEPT 750°C NO FLAME;
HAVE TWO ALTERNATIVE RESINS

2	HOUSING	NATURAL	PA GF
I	CONTATTO (CONTACT)	STAGNATO (TIN-PLATED)	OTTONE (BRASS)
ITEM	DENOMINAZIONE (DESCRIPTION)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN COLOMBO	07MAY99	TE Connectivity			
DIMENSIONS: mm		CHK C. TARTARI	07MAY99	AMP MONO-SHAPE L.I.F TAB CONNECTORS 2-10 POS			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. TURCO	07MAY99				
		PRODUCT SPEC 108-20215					
		APPLICATION SPEC 114-20016					
MATERIAL	FINISH	WEIGHT	SIZE A200779		CAGE CODE C-284338	DRAWING NO	RESTRICTED TO
SEE TABLE	SEE TABLE	CUSTOMER DRAWING		SCALE 2:1	SHEET OF 4	REV D23	

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		2014		REVISIONS	
© COPYRIGHT 2014		BY -		ALL RIGHTS RESERVED.		P	LTR
						-	SEE SHEET 1
						</	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2014

© COPYRIGHT 2014

BY -

ALL RIGHTS RESERVED.

PA GF, UL-V0 GWEPT 750°C NO FLAME, NATURAL

ON TRAY VERSION

No. OF POS	CONFIGURATION (SEE TYP. SECT. ONLY FOR REF.)	P/N ASS'Y 8	PART REV.	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL CODIFICAT. POSITION (FRONT SIDE)	L (mm)	NOTE MARCHIATURA CON BANDA COLORATA	CODICI RAST 5 RICAVABILI
13 2		2293392-2	I	-	-	-	9.9	-	-
13 3		2293392-3	I	-	-	-	14.9	-	-
13 4		2293392-4	I	-	-	-	19.9	-	-
13 5		2293392-5	I	-	-	-	24.9	-	-
13 6		2293392-6	I	-	-	-	29.9	-	-
7		4-2293392-7 13 16	I	IS 6D	-	4D	34.9	-	-
7		2293392-7	D	-	1-2 5-6	-	34.9	-	-
7		1-2293392-7	D	-	1-2 5-6	5S	34.9	-	-
7		2-2293392-7	D	IS 6D	-	4D	34.9	-	-
7		3-2293392-7	D	4D 6D	-	6S	34.9	VIOLET	-
13 8		2293392-8	I	-	-	-	39.9	-	-
13 9		2293392-9	I	-	-	-	44.9	-	-
13 10		1-2293392-0	I	6D 8S	4-5 8-9	6S	49.9	-	-

15

WIRE RETENTION
HOOK ON COVER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±2°

FINISH

SEE TABLE

DWN COLOMBO 07MAY99

CHK C. TARTARI 07MAY99

APVD G. TURCO 07MAY99

PRODUCT SPEC 108-20215

APPLICATION SPEC 114-20016

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME AMP MONO-SHAPE L.I.F
TAB CONNECTORS 2-10 POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A260779C-284338

SCALE 2:1

SHEET 3 OF 4

REV D23

1471-9 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2014

© COPYRIGHT 2014

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SPECIAL VERSION WITH NATURAL COLORED RESIN

No. OF POS	CONFIGURATION (View from top side) 1	ON TRAY PACKAGING VERSION	SIMILAR PN WITH SAME POLARIZASTION	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL CODIFICATION POSITION (FRONT SIDE)	+0.2 L -0.3 (mm)	NOTE STRIP COLOUR	RAST 5 OBTAINABLE CODE
2		5-2301868-3	1-284338-1	2S	1-2	-	9.9	GREY	02-C
2		5-2301868-4	1-284338-4	1D 2S	1-2	-	9.9	GREY	02-A
5		5-2301868-5	293141-2	1S 5D	-	3D	24.9	GREY	-
7		5-2301868-0	293143-1	4D 6D	-	6S	34.9	GREY	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH

0.3

DWN COLOMBO 07MAY99

CHK C. TARTARI 07MAY99

APVD G. TURCO 07MAY99

PRODUCT SPEC 108-20215

APPLICATION SPEC 114-20016

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME AMP MONO-SHAPE L.I.F TAB CONNECTORS 2-10 POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A260779

C-284338

SCALE -

SHEET 4 OF 4

REV D23

1471-9 (3/13)