






Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
Droits de reproduction BERG ELECTRONICS by

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Copyright BERG ELECTRONICS by

PRODUCT NO.
57423



mat'l code				tolerance unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com			
rev.	ecn no.	dr	date	linear	.0 ± .30			title	USB SIDE MOUNT WITH RIGHT SIDE FLANGE			
A	T10144	PP	05/21/'01		.00 ± .20							
B	T20160	WL	05/17/'02		.000± 0.10							
C	T20219	WL	07/11/'02	angles	± 2°			product family	USB	code		
D	T03-0122	WL	4/16/'03	dr	PETER	04/12/'01			unit mm/inch scale		size	dwg no.
E	T04-0196	WL	05/05/'04	enrg	R Y LIU	04/12/'01						
F	N04-0061	PH	10/07/'04	chr	R Y LIU	04/12/'01	appd	A3	57423	sheet 1 OF 2		
				appd	JENN TSAO	04/12/'01						
sheet	revision	F	F									
index	sheet	1	2									

PDM: Rev:F

STATUS: Released

Printed: Jul 28, 2010

Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire de c BERG ELECTRONICS.
Droits de reproduction BERG ELECTRONICS by

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Property of c BERG ELECTRONICS.
Copyright BERG ELECTRONICS by

PRODUCT NO.

57423

PRODUCT NUMBER CODE

57423-X 0 X 0 B LF

HOUSING COLOR OPTION

- 0-WHITE
- 1-BLACK

SHIELD PLATING OPTION

- 1- NICKEL ONLY WITH RIGHT SCREW TYPE 1
- 2- TIN COPPER ALLOY WITHOUT SCREW TYPE 2
- 3- TIN COPPER ALLOY WITH RIGHT SCREW TYPE 1
- 4- TIN COPPER ALLOY WITH LEFT SCREW TYPE 3

TERMINAL PLATING OPTION


- 0-50u" NI UNDERPLATE
- 30u" Au CONTACT AREA
- 100u" TIN/LEAD TAIL AREA IF NO "LF" MARK
- 100u" MATTE TIN TAIL AREA IF WITH "LF" MARK

LEAD FREE MARK


SEE TERMINAL PLATING MARK

NOTES :


- MATERIAL:
CONTACTS: COPPER ALLOY
SHIELD: COPPER ALLOY
HOUSING: UL 94V-0 THERMOPLASTIC, COLOR: SEE PRODUCT CODE
- PLATING: CONTACTS: GOLD FLASH OVER
PALLADIUM NICKEL (0.76um MINIMUM) IN CONTACT AREA; 2.5 um TIN-LEAD OR TIN MINIMUM IN SOLDER TAIL AREA.
1.27 um MINIMUM NICKEL UNDERPLATE OVER ALL SURFACES. SEE PRODUCT NUMBER CODE
SHIELD: SEE PRODUCT NUMBER CODE.
- DATUMS & BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER
- RECOMMENDED BOARD THICKNESS IS 1.20mm.
- MAXIMUM PANEL THICKNESS TO BE 2.67mm IF MOUNTED BEHIND PANEL
- METAL SHELL SLIVER 0.20 MAX.
- ALL COMPONENT PARTS ARE FOLLOWING SONY SS-00259.
- IF LEAD FREE P/N, GS-14-920 SHOULD BE APPLIED
- If lead free p/n, the housing will withstand exposure to 260° peak temperature for 40 seconds in a convection, infra-red or vapor phase reflow oven
- If lead free p/n, the product meets the requirements of the European Union Directive of Restrictions for Hazardous Substances (Directive 2002/95/EC) and can be processed in the process conditions for which the product is developed. FCI, its subsidiaries and affiliates ("FCI") provides the above data and information in good faith based upon current knowledge and experience, but makes no warranty that such data or information is free from error, is complete or is sufficient for user's intended purpose EVEN IF MADE KNOWN TO FCI. FCI specifically disclaims any warranty, express or implied, and assumes no liability with respect to the effectiveness or safety of the products listed above. Each user must make its own determination as to the suitability of FCI's products and materials for its own particular purposes, and must assure that its products fabricated from FCI's products and materials are safe and lawful. It is the user's responsibility to assure proper use and disposal of FCI's products and materials, the safety and health of user's employees and customers, and user's compliance with applicable laws and regulations



WITH LEFT SCREW TYPE '3'



WITHOUT SCREW TYPE '2'



WITH RIGHT SCREW TYPE '1'

mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		A FCI www.fciconnect.com	
rev.	ecn	no.	dr	date	linear	.0 ± .30	projection	title USB SIDE MOUNT WITH SIDE FLANGE	
F						.00 ± .20	⊙		
					angles	.000± 0.10 ± 2°		product family USB	
					dr	PETER 04/12/01	unit	code	
					enr	R Y LIU 04/12/01	mm/inch	size dwg no.	
					chr	R Y LIU 04/12/01	scale	A3 57423	
					appd	JENN TSAO 04/12/01		sheet 2 OF	
sheet	revision								
index	sheet								

PDM: Rev:F

STATUS: Released

Printed: Jul 28, 2010