

Customer Information Sheet

DRAWING No.: MI35X-XX

SHEET 2 OF 2

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

Ø SPECIFICATIONS:

MATERIALS:

MOULDING = PA66 UL94V-2

CONTACT = PHOSPHOR BRONZE

FINISH:

MI352-XX = 0.76µ GOLD OVER 1.2-2.5µ NICKEL

MI353-XX = 5µ 100% TIN OVER 1.2-2.5µ NICKEL

ELECTRICAL:

CURRENT RATING = 5 AMPS

VOLTAGE RATING = 1,500 VRMS

CONTACT RESISTANCE = 5mΩ MAX (GOLD)


MECHANICAL:

INSERTION FORCE = 22.2N MAX (Ø2.03mm PROBE)

WITHDRAWAL FORCE = 2.2N MIN (Ø2.03mm PROBE)

DURABILITY - 100 CYCLES

HARWIN PART No.	COLOUR	FINISH
MI352-94	WHITE	GOLD
MI352-98	BLACK	GOLD
MI352-99	RED	GOLD
MI353-94	WHITE	TIN
MI353-98	BLACK	TIN
MI353-99	RED	TIN



RA	4	25.11.09	10577
NAME	ISS.	DATE	C/NOTE
APPROVED:		R. ADDE	
CHECKED:		M.G. PLESTED	
DRAWN:		R. ADDE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWINHARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.comHARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.ukHARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sgTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATEDMATERIAL:
SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

P.C. MOUNTED TEST JACK

DRAWING NUMBER:

MI35X-XX

SHT
2 OF 2