



New search

Data sheet search

go

Applications | Service | Company

Home » Product line » Process sensors » Pressure sensors » PX9119

PX9119 | PA-0-1PRBN14-B-DVG/US/ / V
Pressure sensors



 Drawing  Wiring



 Interactive product selection (selector)

Datasheet | Accessories | Operating instructions | CAD | More information

☐ Collapse all categories

Product characteristics

Electronic pressure sensor
e1 compliant
Process connection: ¼"NPT A / M5 I
Analogue output
Measuring range: -14.5...0 psi

Application

Application	Type of pressure: relative pressure Liquids and gases
Pressure rating [psi]	145
Bursting pressure min. [psi]	450
Medium temperature [°C]	-25...90

Electrical data

Electrical design	DC
Operating voltage [V]	16...32 DC
Current consumption [mA]	< 18
Insulation resistance [MΩ]	> 100 (500 V DC)
Protection class	III
Reverse polarity protection	yes

Outputs

Output	Analogue output
Output function	10...0 V analogue
Overload protection	yes
Analogue output	10...0 V
Max. load [Ω]	min. 2000

Measuring / setting range

Measuring range [psi]	-14.5...0
-----------------------	-----------

Accuracy / deviations

Accuracy / deviations (in % of the span)	
Characteristics deviation *)	< ± 0.25 (BFSL) / < ± 0.5 (LS)
Repeatability **)	< 0.1
Long-term stability ***)	< ± 0.05

Temperature coefficients (TEMPCO) in the temperature range 0...80° C (in % of the span per 10 K)

Greatest TEMPCO of the zero point	0.15
Greatest TEMPCO of the span	0.2

Reaction times

Step response time analogue output [ms]	3
---	---

Environment

Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 65

Tests / approvals

EMC	EN 61000-4-2 ESD:	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated:	30 V/m
	EN 61000-4-4 Burst:	2 kV
	EN 61000-4-6 HF conducted:	10 V
	radiation of interference	according to the automotive directive 2004/104/EC / CISPR25
	noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2
	HF radiated	100 V/m
Shock resistance	DIN IEC 68-2-27:	50 g (11 ms)
	DIN IEC 68-2-6:	20 g (10...2000 Hz)
MTTF [Years]	531	


Mechanical data

Process connection	¼"NPT A / M5 I
Materials (wetted parts)	stainless steel (303S22); ceramics; FPM (Viton)
Housing materials	stainless steel 316L / 1.4404; FPM (Viton); PA; EPDM/X (Santoprene)
Min. pressure cycles	100 million
Weight [kg]	0.211

Electrical connection

Connection	M12 connector; Gold-plated contacts
------------	-------------------------------------

Wiring



Remarks

Remarks	*) BFSL = Best Fit Straight Line / LS = Limit Value Setting **) with temperature fluctuations < 10 K ***) in % of value of measuring range / 6 months	
Pack quantity [piece]	1	

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — PX9119 — 22.11.2012