

COMPUTER DIODE

Switching

1N4149, 1N4151, 1N4154
1N4446, 1N4447, 1N4448
1N4449

FEATURES

- Metallurgical Bond
- Planar Passivated
- DO-35

DESCRIPTION

This series offers Metallurgical Bonding and is very popular for general purpose switching applications.

5


ABSOLUTE MAXIMUM RATINGS, AT 25°C

	1N4149	1N4151	1N4154	1N4446	1N4447	1N4448	1N4449
Peak Reverse Voltage	.75V	.75V	.35V	.75V	.75V	.75V	.75V
Average Rectified Current				.200mA			
Surge Current, 8.3 mS				.500mA			
Operating Temperature Range				-65°C to +150°C			
Storage Temperature Range				-65°C to +200°C			

ELECTRICAL SPECIFICATIONS (at 25°C unless noted)

Type	Peak Inverse Voltage	Forward Voltage					Reverse Current V_R nA	Reverse Current @ 150°C V_R μ A	Junction Capacitance @ 0V	Reverse Recovery Time t_{RR}
		@ 10mA	@ 20mA	@ 30mA	@ 50mA	@ 100mA				
1N4149	75	1.0	—	—	—	—	20 25	20 50	4pF	4nS
1N4151	75	—	—	—	1.0	—	50 50	50 50	4pF	2nS
1N4154	35	—	—	1.0	—	—	25 100	25 100	4pF	2nS
1N4446	75	—	1.0	—	—	—	20 25	20 50	4pF	4nS
1N4447	75	—	1.0	—	—	—	20 25	20 50	4pF	4nS
1N4448	75	—	—	—	—	1.0	20 25	20 50	4pF	4nS
1N4449	75	—	—	1.0	—	—	20 25	20 50	2pF	4nS

MECHANICAL SPECIFICATIONS



Microsemi Corp.
Watertown
The diode experts