



Specifications:

Approval category	: UL224
Standard	: CSA, LR54949
Approval bodies	: UL
Shrink ratio	: 2:1
Shrink temperature	: 100°C
Minimum operating temperature	: -55°C
Maximum operating temperature	: 135°C

Specification Table

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter	Fully Shrunk Diameter	Flammability Rating	External Length / Height (m)	Reel Length (m)	Part Number
Irradiated polyolefin	Black	20	1.6	0.8	VW-1	150	150	SP16/RL/BLACK
			3.2	1.6				SP32/RL/BLACK
			4.8	2.4				SP48/RL/BLACK
			6.4	3.2		75	75	SP64/RL/BLACK
			9.5	4.7				SP95/RL/BLACK
			12.7	6.3				SP127/RL/BLACK
			19	9.5		60	60	SP190/RL/BLACK
Polyolefin			1.6	0.8		1.2	-	SP16/1.2/BLACK
			2.4	1.2				SP24/1.2/BLACK
			3.2	1.6				SP32/1.2/BLACK
			4.8	2.4				SP48/1.2BLACK
Irradiated polyolefin			6.4	3.2				SP64/1.2BLACK
			9.5	4.7				SP95/1.2/BLACK
			12.7	6.3				SP127/1.2/BLACK
			19	9.5				SP190/1.2/BLACK
			38.1	19				SP381/1.2/BLACK
			50.8	25.4				SP508/1.2/BLACK
			9.5	4.7		5		SP95/5/BLACK
12.7			6.3	SP127/5/BLACK				

Dimensions : Millimetres (Unless Specified)

Specification Table

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter	Fully Shrunk Diameter	Flammability Rating	External Length / Height (m)	Reel Length (m)	Part Number
Irradiated polyolefin	Black	20	25.4	12.7	VW-1	5	-	SP254/5/BLACK
Polyolefin	Clear		2.4	1.2	-	1.2		SP24/1.2/CLEAR
Irradiated polyolefin			6.4	3.2				SP64/1.2/CLEAR
Polyolefin			19	9.5				SP190/1.2/CLEAR
Irradiated polyolefin			6.4	3.2		5		SP64/5/CLEAR
			38.1	19				SP381/5/CLEAR
			2.4	1.2			150	150
			3.2	1.6		SP32/RL/CLEAR		
			4.8	2.4		SP48/RL/CLEAR		
			9.5	4.7		75	75	SP95/RL/CLEAR
			12.7	6.3				SP127/RL/CLEAR
			19	9.5				60
			38.1	19		30	30	SP381/RL/CLEAR
	Polyolefin		Yellow	1.6	0.8	VW-1	1.2	-
2.4				1.2	SP24/1.2/YELLOW			
3.2				1.6	SP32/1.2/YELLOW			
4.8				2.4	SP48/1.2/YELLOW			
6.4				3.2	SP64/1.2/YELLOW			
9.5				4.7	SP95/1.2/YELLOW			
12.7				6.3	SP127/1.2/YELLOW			
19				9.5	SP190/1.2/YELLOW			
25.4				12.7	SP254/1.2/YELLOW			
38.1				19	SP381/1.2/YELLOW			
Polyolefin				50.8	25.4			
Irradiated polyolefin				1.6	0.8		5	SP16/5/YELLOW

Dimensions : Millimetres (Unless Specified)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.