

Industrial PC - IPC 1100 PM 1,1 DE - 2893930

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Industrial PC without display, 1 slot, Pentium M 1.1 GHz, Windows XP German.

Product Description

Industrial PCs – Compact and robust!

The fanless industrial PC 1100 PM 1,1 is especially suitable for use as a PC-based control system for machines and systems in harsh environments. The PLC offers the industry PC a powerful platform with the option of a direct fieldbus connection. Industrial PCs from Phoenix Contact offer guaranteed safety for industrial applications. The IPC 1100 PM 1,1 is equipped with all important PC interfaces as a standard feature.

RoHS

Key Commercial Data

Packing unit	1
GTIN	 4 046356 079068
GTIN	4046356079068
Custom tariff number	84715000

Technical data

Dimensions

Outer dimensions: width, height, depth	201 mm x 303 mm x 110 mm
--	--------------------------

Computer data

Processor	Intel®Pentium® M 1,1 GHz
Cooling	passive
Operating system	Windows® XP, German
RAM	512 MB DDR SODIMM
Mass storage	2.5" HDD, min. 40 GB (UDMA)
Network	2 x Ethernet (10/100 Mbps), RJ45

Industrial PC - IPC 1100 PM 1,1 DE - 2893930

Technical data

Computer data

Interfaces	COM 1, COM 2, COM 3 (RS-232), 1x DVI, 1x PS/2 mouse, 1x PS/2 keyboard, 3x USB
Monitor output	DVI
Slots	1x PCI
Optical drive	No CD-ROM
Graphics card	On-board graphics chip (AGP)

General

Mounting type	on mounting plate
Weight	3400 g

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	5 °C ... 40 °C
Permissible humidity (operation)	10 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 85 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-29

Standards and Regulations

Shock	DIN EN 60068-2-29
Vibration (operation)	DIN EN 60068-2-6

Classifications

eCl@ss

eCl@ss 4.0	27250281
eCl@ss 4.1	27360102
eCl@ss 5.0	27360102
eCl@ss 5.1	27360102
eCl@ss 6.0	27242301
eCl@ss 8.0	19200101
eCl@ss 9.0	19200101

ETIM

ETIM 2.0	EC001414
ETIM 3.0	EC001414
ETIM 4.0	EC001414
ETIM 5.0	EC001413

Industrial PC - IPC 1100 PM 1,1 DE - 2893930

Classifications

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43211507
UNSPSC 13.2	43201404

Accessories

Accessories

Security router without DIN rail mounting

Router - FL MGuard PCI/533 - 2989213



Firewall/router in PCI format 533 MHz processor cycle frequency

Router - FL MGuard PCI/533 VPN - 2989417



Firewall/router in the PCI format 533 MHz processor cycle frequency and VPN

Router - FL MGuard PCI/266 - 2989019



Firewall/router in PCI format 266 MHz processor cycle frequency

Industrial PC - IPC 1100 PM 1,1 DE - 2893930

Accessories

Router - FL MGuard PCI/266 VPN - 2989514



Firewall/router in PCI format 266 MHz processor cycle frequency and VPN