




参考基板レイアウト (マウント面)
P.W. BOARD PATTERN DIMENSION (REFERENCE)
(MOUNTING AREA)


注記 NOTES:

1. 使用材料 MATERIAL
ハウジング: 液晶ポリマー (LCP) ガラス充填 UL94V-0 (黒)
HOUSING: LIQUID CRYSTAL POLYMER (GLASS FILLED)
UL94V-0 (COLOR: BLACK)
ターミナル: リン青銅 (t=0.15)
TERMINAL: PHOSPHOR BRONZE (t=0.15)
金具: リン青銅 (t=0.15)
FITTING NAIL: PHOSPHOR BRONZE (t=0.15)
2. メッキ仕様 PLATING
ターミナル TERMINAL
金メッキ 0.2マイクロメートル以上 (コンタクト部)
GOLD 0.2MICROMETER MINIMUM (CONTACT AREA)
金メッキ 0.4マイクロメートル以下 (テール部)
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
下地メッキ: ニッケルメッキ 1.5マイクロメートル以上
UNDER PLATING: NICKEL 1.5MICROMETER MINIMUM
*コンタクト部とテール部はニッケルメッキによって分断されている金メッキです。
DIVIDE INTO PARTS THE GOLD PLATING OF THE CONTACT AND THE TAIL PART BY THE NICKEL PLATING.
金具 FITTING NAIL
錫メッキ 1.0 マイクロメートル以上
TIN PLATING 1.0 MICROMETER MINIMUM
下地メッキ: ニッケルメッキ 1.0 マイクロメートル以上
UNDER PLATING: NICKEL 1.0 MICROMETER MINIMUM
3. (全極数/2) = 偶数の場合に適用。
APPLY FOR (CIRCUIT/2) = EVEN.
4. 嵌合相手: 55909シリーズ
MATE WITH: 55909 SERIES.
5. テール平坦度は、0.08以下
テール及び金具の平坦度は、0.1以下
TAIL COPLANARITY TO BE 0.08 MAXIMUM
TAIL AND FITTING NAIL COPLANARITY TO BE 0.1 MAXIMUM
6. 同一回路以外のパターン書込み禁止範囲を示す。
NO PRINT CIRCUIT AREA OTHER THAN THE SAME CIRCUIT.
7. 本製品は 51338-***3 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 51338-***3.
8. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT

REVISED	EC NO: J2010-2586 DRWN:YON002 CHKD:S. MARUYAMA APPR:MSASAO	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	CONNECTOR SERIES No.: 51338-***9	
					MM ONLY		---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
			10 UNDER	± 0.2	DRAWN BY Y. NUKANOBU	DATE 2010/01/25	TITLE 0.4 B-TO-B REC ASSY HGT=1.5 J-BEND TAIL		
			10 OVER 30 UNDER	± 0.25	CHECKED BY S. MARUYAMA	DATE 2010/01/25			
			30 OVER	± 0.3	APPROVED BY M. SASAO	DATE 2010/01/25			
			ANGULAR ±3 °		MATERIAL NO.		 MOLEX INCORPORATED		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 1		DOCUMENT NO. SD-51338-005	SHEET NO. 2 OF 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

NOTES

- 製品詳細寸法については、SD-51338-005 を参照下さい。
RE DETAILED DIMENSION, SEE PRODUCT DRAWING SD-51338-005.
- 梱包数量：2500個/リール
NUMBER OF CONNECTORS : 2500PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH




4.材料

キャリアテープ : PS
トップテープ : PS, OTHER
リール : PS<リサイクル材を含む>


MATERIAL

CARRIER TAPE : PS
TOP TAPE : PS, OTHER
REEL : PS <RECYCLE MATERIAL CONTAINED>

- 5.ELV 及び RoHS 適合品。
ELV AND RoHS COMPLIANT.



REVISED EC NO: J2015-0987 DRAWN: KMIYAHARA 2015/01/27 CHKD: KTANAKA03 2015/09/07 APPR: KMORIKAWA 2015/09/11 A	DESCRIPTION A	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		0.25 UNDER	UNDER	± 0.03	DRAWN BY	DATE	TITLE 0.4 B-TO-B CONN. REC HSG ASSY(HGT=1.5) EMBSTP PKG			
		0.25 OVER	0.5 UNDER	± 0.05	YON002	2010/06/23				
		0.5 OVER	1.0 UNDER	± 0.1	CHECKED BY	DATE				
		1.0 OVER	10 UNDER	± 0.2	APPROVED BY	DATE				
		10 OVER	30 UNDER	± 0.25	MSASAO	2010/06/29	molex			
		30 OVER		± 0.3	MATERIAL NO.					DOCUMENT NO.
		ANGULAR ±3 °			SEE CHART		SD-51338-006			1 OF 2
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



注記)製品がポケット内に問題なく納まること。
NOTE. Pocket should contain product smoothly.

24	29.4	25.4	16.06	51338-6473	64
			14.06	51338-5473	54
			12.06	51338-4473	44
			5.26	51338-9873	10
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	オーダー番号 ORDER NO.	極数 CIRCUITS

REVISED EC NO: J2015-0987 DFWNGKMIYAHARA 2015/01/27 CHKDK:TANKAKO3 2015/09/17 APPR:KMOIRIKAWA 2015/09/11	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
		0.25 UNDER UNDER ±0.03	DRAWN BY DATE		TITLE 0.4 B-TO-B CONN. REC HSG ASSY(HGT=1.5) EMBSTP PKG						
		0.25 OVER 0.5 UNDER ±0.05	YON002 2010/06/23								
		0.5 OVER 1.0 UNDER ±0.1	CHECKED BY DATE								
		1.0 OVER 10 UNDER ±0.2	APPROVED BY DATE								
		10 OVER 30 UNDER ±0.25	MSASAO 2010/06/29								
		30 OVER ±0.3	MATERIAL NO.							DOCUMENT NO.	
	ANGULAR ±3 °	SEE CHART		SD-51338-006			2 OF 2				
REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
A											