

PM20-24S DC-DC Converters

The PM20 is a DC-DC converter which provides a regulated output at power levels up to 20 watts. It accepts a wide range DC input and provides a fully isolated, regulated output. In operation, either (or neither) input pin, as well as either (or neither) output pin can be grounded.* PM20 units provide full output power for ambient temperatures up to 60°C, with linear derating from 60°C to zero power at 105°C. In forced air applications, full output power can be maintained as long as the chassis temperature, as measured in the center of the unit's label, is maintained at less than or equal to 100°C.

* Note : For safety agency approval of the end use equipment to safety standards (such as UL-1950, CSA 22.2-950, DIN VDE 0805 and EN60950), the output of the converter is ELV if the input to the converter is ELV; the output of the converter is SELV only if its input is SELV. The input and output are to be both floating or both grounded. The converter is to be protected by the specified fuse, provided in the ungrounded leg.


Specifications:

ITEMS		MODEL	PM20-24S Series			
			PM20-24S03	PM20-24S05	PM20-24S12	PM20-24S15
Nominal Output Voltage	V	3.3	5	12	15	
Voltage Accuracy	-	± 1%				
Output Current (Power) @ 60°C	A/W	5.00 (16.5)	4.00 (20.0)	1.67 (20.0)	1.33 (20.0)	
Operating Temperature	-	-25°C to +105°C. Derate linearly above +60°C to 0 watts at 105°C				
Output Voltage Adjustment Range	V	3.3 - 3.6	4.5 - 5.5	10.8 - 13.2	13.5 - 16.5	
Output Ripple (20MHz BW)	mV	20mV RMS / 75mV p-p		25mV RMS / 100mV p-p		
Line Regulation	mV	6.6	10	24	30	
Load Regulation (10% - 100%)	mV	33	50	120	150	
Remote Voltage Programming	-	+10% Programming				
Remote On / Off	-	Logic 1 or open enables unit, logic 0 or short shuts unit down. Referenced to -Vin				
Temperature Coefficient	-	± 0.01% / °C				
Overshoot	-	No overshoot at turn on, turn off, power failure or removal of a short circuit				
Input Voltage Range	-	18 - 36Vdc				
Efficiency (Typical)	%	76	81			
No Load Input Power	W	0.4				
Short Circuit Protection	-	Continuous				
Overvoltage Clamp Point (fixed)	V	4.7 max.	6.5 max.	14 max.	17.5 max.	
Isolation (Input to Output)	-	500Vac, 700Vdc, 10MΩ				
Regulatory Agency Compliance**	-	UL1950, EN60950, CSA22.2-234				
Mounting & Connections	-	0.040" diameter, 0.22" long solderable pins				
Cover	-	0.032" anodized aluminum				
Size (W.H.D.)	in	1.6" x 2.0" x 0.335"				
Storage Temperature	-	-40°C to +105°C				
Cooling	-	Convection cooling allows full o/p rating. Contact factory for rating w/external forced air				
Vibration	-	2.5G RMS, 10Hz - 50Hz, random vibration, 10 minutes per axis				
Relative Humidity	-	5% - 95%, non-condensing				
Altitude	-	10,000 feet max. operating / 45,000 feet max. storage				
Fungus Proofing	-	Units are inherently fungus inert				
Thermal Cycling	-	1 hour @ -25°C ramped to 1 hour @ +25°C ramped to 1 hour @ +100°C, 10 cycles, ramp = 5°C/minute				
Warranty	-	2 year warranty includes parts and labor				


** Regulatory Agency compliance testing is in process. Check individual unit's label for appropriate agency logos.

Note : Regulation values pertain to operation with output currents above 10% of rated load current on main output.

Recommended Circuit Hook up:




- Notes:
1. Input can have -Vin, +Vin or neither terminal grounded. Input ground connection should be placed as close to PM unit input as possible.
 2. Output can have -Vo, +Vo or neither terminal grounded. Output ground connection should be placed as close to PM unit as possible.
 3. An optional low impedance capacitor can be added at the input terminals of the PM20 unit to reduce reflected ripple current to the DC source.
 4. Recommended input fusing: 3A (Buss PCB3, or equivalent)
 5. Remote on/off control: low impedance path, or logic 0, referenced to -Vin disables unit output. Open circuit, or logic 1, referenced to -Vin enables output.
 6. Output voltage programming: Resistor connected from Pin 8 to either -V or +V will generate increased or decreased output voltages, respectively, as follows.



Mechanical Information:

PM20 units are designed for installation on printed wiring boards. Input and output pin headers have 0.010" insulating bosses built in to provide clearance between the headers and the installation PC board to allow for wave soldering. During wave soldering, the top surface of the board to which the PM unit is mounted (measured 1/2" from the edge of the PM unit) should be maintained at a temperature of no more than 180°C for no more than 30 seconds. The chassis of the PM unit is electrically isolated from both the input and output circuitry and should be left floating in a typical installation.



Total Output Power vs. Ambient Operating Temperature

