





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	.270 [6.86]	SIGNAL
T	.270 [6.86]	SIGNAL
S	.270 [6.86]	SIGNAL
R	.270 [6.86]	SIGNAL
PA	N/A [N/A]	POWER
HA	N/A [N/A]	HOLD-DOWN
E	.220 [5.59]	SIGNAL

PRODUCT NO.	ROWS	POWER				SIG.			POWER			E2
		E1	P1	P2	P3	1	2	3	P4	P5	P6	
51730-079-- NOTE: 3	D C B A		PA	PA	PA	UUU TTT SSS EEE			PA	PA	PA	
												



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date					COPY		projection		title	
A	V03-0683	MEM	6/18/03			linear	.XX±.01/0.X±0.3					3P + 12S + 3P	
B	DG05-0300	GuoJM	08/26/05				.XXX±.005/0.XX±0.13					RIGHT ANGLE SOLDER HEADER	
C	DG05-0560	CS	12/26/05			angles	.XXX±.0020/0.XXX±0.051					product family	PwrBlade
D	DG08-0253	SH	09/13/08				0°±2°					size	213
						dr	M. MOSTOLLER	6/18/03				dwg no	51730-079
						enrg	M. MOSTOLLER	6/18/03				scale	1 of 4
						chr	H. BREWBAKER	6/18/03					
						appd	M. MOSTOLLER	6/18/03					
sheet index	revision sheet	D	D	D	D							cage code	22526
		1	2	3	4								

Pro/E

PDM: Rev:D

STATUS:Released


Printed: Dec 20, 2010

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.


PRODUCT NUMBER
51730-079--
NOTE: 3




BROKEN-OUT SECTION A-A
SCALE 2:1



BROKEN-OUT SECTION B-B
SCALE 2:1



SECTION C-C

mat'l code				SEE NOTE 2				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com											
litr		ecn no.		dr		date		linear		.XX±.01/0.X±0.3				COPY													
D										.XXX±.005/0.XX±0.13				title								3P + 12S + 3P					
										.XXX±.0020/0.XXX±0.051				RIGHT ANGLE SOLDER HEADER													
								angles		0°±2°				INCH/MM				product family				PwrBlade				code	
								dr		M. MOSTOLLER 6/18/03				scale				size				dwg no				213	
								engr		M. MOSTOLLER 6/18/03								A				51730-079				sheet	
								chr		H. BREWBAKER 6/18/03																2 of 4	
								appd		M. MOSTOLLER 6/18/03																	
sheet index		revision sheet																									

cage code 22526


A

B

1 | 2

3

4



RECOMMENDED PCB LAYOUT

[illegible]

coge code	22526
-----------	-------

1	2
---	---

Pro/E

3

4

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.

A



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

B

1 | 2

3 |

4

PRODUCT NUMBER
51730-079--
NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

3. PLATING:
A SEE ITEM 1 & 2 IN PRINT 10064183 FOR PLATING SPEC OF 51730-079 AND 51730-079LF RESPECTIVELY

4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

9. $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.

10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

11. CONNECTOR KEEP-OUT ZONE.

12: A A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW,
OR NOTE WHICH HAS BEEN MODIFIED WITH CURRENT
DRAWING VERSION.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com				
litr	ecn no.	dr	date	linear	$.XX \pm .01 / 0.X \pm 0.3$		COPY			title 3P + 12S + 3P RIGHT ANGLE SOLDER HEADER				
D					$.XXX \pm .005 / 0.XX \pm 0.13$		projection							
					$.XXX \pm .0020 / 0.XXX \pm 0.051$									
				angles	$0^\circ \pm 2^\circ$				product family PwrBlade					
				dr	M. MOSTOLLER	6/18/03	INCH/MM							
				enrg	M. MOSTOLLER	6/18/03	scale							
				chr	H. BREWBAKER	6/18/03	1:1		size		dwg no	code		
				appd	M. MOSTOLLER	6/18/03			A		51730-079		213 sheet 4 of 4	
sheet index		revision sheet												

A

B

1 | 2

Pro/E

3 |

cage code 22526

4