



0291




0291-0-15-XX-16-XX-10-0
Hex press-fit in .067 plated
thru hole

0293




0293-0-15-XX-16-XX-10-0
Press-fit in .067 mounting hole

0287




0287-0-15-XX-16-XX-10-0
Solder mount in .065 min. mounting hole
Also available on 8mm wide carrier
tape: 3,250 parts per 13" reel.
Order as: 0287-0-57-XX-16-XX-10-0

0285




0285-0-15-XX-16-XX-10-0
Solder mount in .065 min.
mounting hole

0284




0284-0-15-XX-16-XX-10-0
Solder mount in .070 min.
mounting hole

8114




8114-0-15-XX-16-XX-04-0
Press-fit from underside of pc board
into .065 mounting hole

0407




0407-0-15-XX-16-XX-04-0
Press-fit in .066 mounting hole

0415




0415-0-15-XX-16-XX-10-0
Solder mount in .063 min. mounting hole
Also available on 24mm wide carrier
tape: 1,500 parts per 13" reel.
Order as: 0415-0-57-XX-16-XX-10-0

0303




0303-0-19-XX-16-XX-10-0
Wire Termination
Press-fit in .067 mounting hole

0306




0306-0-19-XX-16-XX-10-0
Wire Termination
#18 gage crimp barrel

0273



0273-0-15-XX-16-XX-10-0
Press-fit in .078 mounting hole

7520



7520-0-15-XX-16-XX-10-0
Press-fit in .066 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
27 30μ" GOLD OVER NICKEL



CONTACT

#16 CONTACT (DATA ON PAGE 221)