


Models 72929
Mini SMD Grabber Test Clip Lead with 4mm Jack



Features

- SMD Grabber Test Clip (Pomona 72906) with 20 Inch(50cm) lead
- 4mm Jack for easy attachment to DMM leads.

Materials

Grabber End:

- Insulation: Polyamide
- Jaws: Steel

Jack End:

- Insulation: Polypropylene
- Socket Body: Nickel plated Brass

Ordering Information

Model: 72929-20-Color
Black (-0) or Red (-2)

Specifications

Max Current Admissible	1A
Voltage; Max - Tension	33 V AC / 70 V DC

Rating: *hands free testing* in controlled environment:
70Vrms max. For CE compliance: Not intended for hand-held use at voltages above 33Vrms/70Vdc

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.