



BZX84J series

Voltage regulator diodes

Rev. 3 — 27 February 2025

Product data sheet

1. General description

General-purpose Zener diodes in a SOD323F (SC-90) very small and flat lead Surface-Mounted Device (SMD) plastic package.

2. Features and benefits

- Non-repetitive peak reverse power dissipation: ≤ 100 W for types ≤ 6.8 V
- Non-repetitive peak reverse power dissipation: ≤ 40 W for types ≥ 7.5 V
- Total power dissipation: $P_{\text{tot}} \leq 550$ mW
- Wide working voltage range: nominal 2.4 V to 75 V (E24 range)
- Two tolerance series: $\pm 2\%$ and $\pm 5\%$
- Small plastic package suitable for surface-mounted design
- Low differential resistance
- AEC-Q101 qualified

3. Applications

- General regulation functions

4. Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
V_F	forward voltage	$I_F = 100$ mA	[1]	-	-	1.1	V
P_{ZSM}	non-repetitive peak reverse power dissipation		[2]	-	-	100	W
			[3]	-	-	40	W



[1] pulsed; $t_p \leq 300$ μ s; $\delta \leq 0.02$

[2] pulsed; $t_p = 100$ μ s; square wave; $T_j = 25$ °C prior to surge; ≤ 6.8 V

[3] pulsed; $t_p = 100$ μ s; square wave; $T_j = 25$ °C prior to surge; ≥ 7.5 V

5. Pinning information

Table 2. Pinning

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	K	cathode[1]		 006aaa152
2	A	anode		

[1] The marking bar indicates the cathode.

6. Ordering information

Table 3. Ordering information

Type number	Package		
	Name	Description	Version
BZX84J-B2V4 to BZX84J-C75 ^[1]	SC-90	plastic surface-mounted package; 2 leads	SOD323F

[1] The series consists of 74 types with nominal working voltages from 2.4 V to 75 V.

7. Marking

Table 4. Marking Codes

Type number	Mark. Code	Type number	Mark. Code	Type number	Mark. Code	Type number	Mark. Code
BZX84J-B2V4	SL	BZX84J-B15	SC	BZX84J-C2V4	U3	BZX84J-C15	TV
BZX84J-B2V7	SM	BZX84J-B16	SD	BZX84J-C2V7	U4	BZX84J-C16	TW
BZX84J-B3V0	ST	BZX84J-B18	SE	BZX84J-C3V0	U9	BZX84J-C18	TX
BZX84J-B3V3	SU	BZX84J-B20	SF	BZX84J-C3V3	UA	BZX84J-C20	TY
BZX84J-B3V6	SV	BZX84J-B22	SG	BZX84J-C3V6	UB	BZX84J-C22	TZ
BZX84J-B3V9	SW	BZX84J-B24	SH	BZX84J-C3V9	UC	BZX84J-C24	U1
BZX84J-B4V3	SZ	BZX84J-B27	SK	BZX84J-C4V3	UF	BZX84J-C27	U2
BZX84J-B4V7	TA	BZX84J-B30	SN	BZX84J-C4V7	UG	BZX84J-C30	U5
BZX84J-B5V1	TD	BZX84J-B33	SP	BZX84J-C5V1	UL	BZX84J-C33	U6
BZX84J-B5V6	TE	BZX84J-B36	SR	BZX84J-C5V6	UM	BZX84J-C36	U7
BZX84J-B6V2	TH	BZX84J-B39	SS	BZX84J-C6V2	UR	BZX84J-C39	U8
BZX84J-B6V8	TK	BZX84J-B43	SX	BZX84J-C6V8	US	BZX84J-C43	UD
BZX84J-B7V5	TM	BZX84J-B47	SY	BZX84J-C7V5	UU	BZX84J-C47	UE
BZX84J-B8V2	TN	BZX84J-B51	TB	BZX84J-C8V2	UV	BZX84J-C51	UH
BZX84J-B9V1	TP	BZX84J-B56	TC	BZX84J-C9V1	UW	BZX84J-C56	UK
BZX84J-B10	S8	BZX84J-B62	TF	BZX84J-C10	TR	BZX84J-C62	UN
BZX84J-B11	S9	BZX84J-B68	TG	BZX84J-C11	TS	BZX84J-C68	UP
BZX84J-B12	SA	BZX84J-B75	TL	BZX84J-C12	TT	BZX84J-C75	UT
BZX84J-B13	SB	-	-	BZX84J-C13	TU	-	-

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
I _F	forward current			-	250	mA
I _{ZSM}	non-repetitive peak reverse current		[1]	-	see Tables 8 and 9	
P _{ZSM}	non-repetitive peak reverse power dissipation		[2]	-	100	W
			[3]	-	40	W
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[4]	-	550	mW
T _j	junction temperature			-	150	°C
T _{amb}	ambient temperature			-55	+150	°C
T _{stg}	storage temperature			-65	+150	°C

- [1] t_p = 100 μs; square wave; T_j = 25 °C prior to surge.
- [2] t_p = 100 μs; square wave; T_j = 25 °C prior to surge; ≤ 6.8 V.
- [3] t_p = 100 μs; square wave; T_j = 25 °C prior to surge; ≥ 7.5 V.
- [4] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm².

9. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
R _{th(j-a)}	thermal resistance from junction to ambient	in free air	[1].	-	-	230	K/W
R _{th(j-sp)}	thermal resistance from junction to solder point		[2]	-	-	55	K/W

- [1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated, mounting pad for cathode 1 cm²
- [2] Soldering point of cathode tab.

10. Characteristics

Table 7. Electrical characteristics

T_j = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions		Max	Unit
V _F	forward voltage	I _F = 10 mA	[1]	0.9	V
		I _F = 100 mA		1.1	V

- [1] Pulse test: t_p ≤ 300 μs; δ ≤ 0.02

Table 8. Electrical characteristics per type; BZX84J-B2V4 to BZX84J-C24

T_j = 25 °C unless otherwise specified.

BZX84J-x xx	Sel	Working voltage V _Z (V);		Differential resistance r _{diff} (Ω);		Reverse current I _R (μA);		Temperature coefficient S _Z (mV/K);		Diode capacit. C _d (pF) ^[1]	Non-repetitive peak reverse current I _{ZSM} (A) ^[2]
		I _Z = 5 mA		I _Z = 1 mA	I _Z = 5 mA			I _{Ztest} = 5 mA			
		Min	Max	Min	Max	Max	V _R (V)	Min	Max	Max	Max
2V4	B	2.35	2.45	400	100	50	1	-3.5	0	450	12
	C	2.2	2.6								
2V7	B	2.65	2.75	450	100	20	1	-3.5	0	440	12
	C	2.5	2.9								
3V0	B	2.94	3.06	500	95	10	1	-3.5	0	425	12
	C	2.8	3.2								
3V3	B	3.23	3.37	500	95	5	1	-3.5	0	410	12
	C	3.1	3.5								
3V6	B	3.53	3.67	500	90	5	1	-3.5	0	390	12
	C	3.4	3.8								
3V9	B	3.82	3.98	500	90	3	1	-3.5	0	370	12
	C	3.7	4.1								
4V3	B	4.21	4.39	600	90	3	1	-3.5	0	350	12
	C	4.00	4.60								
4V7	B	4.61	4.79	500	80	3	2	-3.5	0.2	325	12
	C	4.40	5.00								
5V1	B	5.00	5.20	480	60	2	2	-2.7	1.2	300	12
	C	4.80	5.40								
5V6	B	5.49	5.71	400	40	1	2	-2.0	2.5	275	12
	C	5.20	6.00								
6V2	B	6.08	6.32	150	10	3	4	0.4	3.7	250	12
	C	5.80	6.60								
6V8	B	6.66	6.94	80	15	2	4	1.2	4.5	215	12
	C	6.40	7.20								
7V5	B	7.35	7.65	80	10	1	5	2.5	5.3	170	4
	C	7.00	7.90								
8V2	B	8.04	8.36	80	10	0.7	5	3.2	6.2	150	4
	C	7.70	8.70								
9V1	B	8.92	9.28	100	10	0.5	6	3.8	7.0	120	3
	C	8.50	9.60								
10	B	9.80	10.20	150	10	0.2	7	4.5	8.0	110	3
	C	9.40	10.60								
11	B	10.78	11.22	150	10	0.1	8	5.4	9	108	2.5
	C	10.40	11.60								
12	B	11.80	12.20	150	10	0.1	8	6.0	10	105	2.5
	C	11.40	12.70								

BZX84J-x xx	Sel	Working voltage V _Z (V);		Differential resistance r _{diff} (Ω);		Reverse current I _R (μA);		Temperature coefficient S _Z (mV/K);		Diode capacit. C _d (pF)[1]	Non- repetitive peak reverse current I _{ZSM} (A)[2]
		I _Z = 5 mA		I _Z = 1 mA	I _Z = 5 mA			I _{Ztest} = 5 mA			
		Min	Max	Min	Max	Max	V _R (V)	Min	Max	Max	Max
13	B	12.70	13.30	170	10	0.1	8	7.0	11	103	2.5
	C	12.40	14.10								
15	B	14.70	15.30	200	15	0.05	10.5	9.2	13	99	2.0
	C	13.80	15.60								
16	B	15.70	16.30	200	20	0.05	11.2	10.4	14	97	1.5
	C	15.30	17.1								
18	B	17.60	18.40	225	20	0.05	12.6	12.4	16	93	1.5
	C	16.80	19.10								
20	B	19.60	20.40	225	20	0.05	14.0	14.4	18	88	1.5
	C	18.80	21.20								
22	B	21.60	22.40	250	25	0.05	15.4	16.4	20	84	1.25
	C	20.80	23.30								
24	B	23.50	24.50	250	30	0.05	16.8	18.4	22	80	1.25
	C	22.80	25.6								


[1] f = 1 MHz; V_R = 0 V
[2] t_p = 100 μs; square wave; T_J = 25 °C prior to surge.

Table 9. Electrical characteristics per type; BZX84J-B27 to BZX84J-C75

T_j = 25 °C unless otherwise specified.


BZX84J-x xx	Sel	Working voltage V _Z (V);		Differential resistance r _{diff} (Ω);		Reverse current I _R (μA);		Temperature coefficient S _Z (mV/K);		Diode capacit. C _d (pF) ^[1]	Non- repetitive peak reverse current I _{ZSM} (A) at t _p = 100 μs; T _{amb} = 25°C
		I _Z =2 mA		I _Z = 0.5 mA	I _Z =2 mA			I _{Ztest} =2 mA			
		Min	Max	Min	Max	Max	V _R (V)	Min	Max	Max	Max
27	B	26.5	27.5	250	40	0.05	18.9	21.4	25.3	73	1
	C	25.1	28.9								
30	B	29.4	30.6	250	40	0.05	21.0	24.4	29.4	66	1
	C	28.0	32.0								
33	B	32.3	33.7	275	40	0.05	23.1	27.4	33.4	60	0.9
	C	31.0	35.0								
36	B	35.3	36.7	300	60	0.05	25.2	30.4	37.4	59	0.8
	C	34.0	38.0								
39	B	38.2	39.8	300	75	0.05	27.3	33.4	41.2	58	0.7
	C	37.0	41.0								
43	B	42.1	43.9	325	80	0.05	30.1	37.6	46.6	56	0.6
	C	40.0	46.0								
47	B	46.1	47.9	325	90	0.05	32.9	42.0	51.8	55	0.5
	C	44.0	50.0								
51	B	50.0	52.0	350	110	0.05	35.7	46.6	57.2	52	0.4
	C	48.0	54.0								
56	B	54.9	57.1	375	120	0.05	39.2	52.2	63.8	49	0.3
	C	52.0	60.0								
62	B	60.8	63.2	400	140	0.05	43.4	58.8	71.6	44	0.3
	C	58.0	66.0								
68	B	66.6	69.4	400	160	0.05	47.6	65.6	79.8	40	0.25
	C	64.0	72.0								
75	B	73.5	76.5	400	175	0.05	52.5	73.4	88.6	35	0.2
	C	70.0	79.0								

[1] f = 1 MHz; V_R = 0 V




- (1) 2.4 V to 6.8 V ($T_j = 25\text{ °C}$)
- (2) 7.5 V to 75 V ($T_j = 25\text{ °C}$)
- (3) 2.4 V to 75 V ($T_j = 150\text{ °C}$)

Fig. 1. Non-repetitive peak reverse power dissipation as a function of pulse duration; maximum values




$T_j = 25\text{ °C}$

Fig. 2. Forward current as a function of forward voltage; typical values (BZX84J-B/C2V4-Q)



$T_j = 25\text{ °C}$

Fig. 3. Forward current as a function of forward voltage; typical values (BZX84J-B/C6V8)



$T_j = 25\text{ °C}$

Fig. 4. Forward current as a function of forward voltage; typical values (BZX84J-B/C7V5)




Fig. 5. Forward current as a function of forward voltage; typical values (BZX84J-B/C75)




Fig. 6. Temperature coefficient as a function of working current; typical values (BZX84J-B/C2V4 to B/C4V7)




Fig. 7. Temperature coefficient as a function of working current; typical values (BZX84J-B/C5V1 to B/C15)




Fig. 8. Reverse current as a function of reverse voltage; typical values (BZX84J-B/C2V4 to B/C6V8)




Fig. 9. Reverse current as a function of reverse voltage; typical values (BZX84J-B/C7V5 to B/C24)




Fig. 10. Reverse current as a function of reverse voltage; typical values (BZX84J-B/C27 to B/C75)

11. Test information

11.1. Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

12. Package outline




Fig. 11. Package outline SC-90 (SOD323F)

13. Soldering




Fig. 12. Reflow soldering footprint SC-90 (SOD323F)

14. Revision history

Table 10. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BZX84J_SER v.3	20250227	Product data sheet	-	BZX84J_SER v.2
Modifications:	- Quick reference data and Limiting values: Values at P_{ZSM} improved - Characteristics: Figures adapted to newest improved versions if applicable			
BZX84J_SER v.2	20110801	Product data sheet	-	BZX84J_SER v.1
BZX84J_SER v.1	20070301	Product data sheet	-	-

15. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <https://www.nexperia.com>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description..... 1

2. Features and benefits..... 1

3. Applications..... 1

4. Quick reference data..... 1

5. Pinning information..... 1

6. Ordering information..... 2

7. Marking..... 2

8. Limiting values..... 3

9. Thermal characteristics..... 3

10. Characteristics..... 3

11. Test information..... 9

11.1. Quality information..... 9

12. Package outline..... 10

13. Soldering..... 10

14. Revision history..... 11

15. Legal information..... 12

© Nexperia B.V. 2025. All rights reserved

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 27 February 2025