



3. CABLE SHOULD HAVE TOLERANCE OF $\pm 0.25'$ UPTO 12 INCH LENGTH,
 $\pm 0.50'$ FOR LONGER CABLES.



SEE NOTE 3

PART NUMBER	LENGTH (IN.)
135101-R1-03.00	3.00
135101-R1-04.00	4.00
135101-R1-05.00	5.00
135101-R1-06.00	6.00
135101-R1-07.00	7.00
135101-R1-08.00	8.00
135101-R1-09.00	9.00
135101-R1-10.00	10.00
135101-R1-11.00	11.00
135101-R1-12.00	12.00
135101-R1-18.00	18.00
135101-R1-24.00	24.00

☐ FREQUENCY _____ TO _____ GHz
 ☒ CONTINUITY
☐ VSWR _____ : 1 MAX
 ☒ HI-POT : 750 VRMS
☐ INS. LOSS _____ dB MAX
 ☐ OTHER _____

009-881-380	A/R	2	CONFORMABLE 0.085" CABLE	
132101	2	1	SMA STR PLUG	
PART NUMBER	QTY	ITEM	DESCRIPTION	FINISH

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp. or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or privileges in or to any invention, design, process, use or sale of any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

DRAWN	DATE
CLEMENT	19-Mar-10
ENGINEER	DATE
CLEMENT	19-Mar-10
APPROVED	DATE
CAD FILE	
Root folder:/Cable assembly/135101-R1-XX.XX	

DWG SIZE	B
----------	---

REV
A

Amphenol
Connex

SCALE: 2.3:1	SHEET 1 OF 1
--------------	--------------