


OPERATING CHARACTERISTICS AT T _A = 25°C					
LED CHARACTERISITICS	MIN.	TYP.	MAX.	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	880		2500	mcd	I _F = 20 mA
VIEWING ANGLE (2 θ 1/2)		30		deg.	
FORWARD VOLTAGE		3.8	4.0	V	I _F = 20 mA
REVERSE CURRENT	10			μA	V _R = 5 V

ABSOLUTE MAXIMUM RATINGS AT T _A = 25°C		
PARAMETER	VALUE	UNITS
DC FOWARD CURRENT	30	mA
PEAK FORWARD CURRENT	100	mA
POWER DISSIPATION	120	mW
REVERSE VOLTAGE (I _R = 10μA)	5	V
OPERATING TEMPERATURE RANGE	-40 to +80	°C
STORAGE TEMPERATURE RANGE	-40 to +100	°C
DIP-DRAG SOLDER TEMPERATURE	260 FOR 5 SECS.	°C

REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	—	NEW RELEASE	JAV			

NOTES:

1. LENS COLOR: WHITE.
2. LEADS: SOLDER DIP MILD STEEL.
3. LEAD SPACING MEASURED NEAR EPOXY PACKAGE.
4. SOLDER ADHERANCE: BOTH LEADS PER MIL. STD. 202E, METHOD 208C.
5. ATTENTION: OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC SENSITIVE DEVICES. FOR EYE SAFTEY DO NOT STARE DIRECTLY INTO THE LIGHT BEAM OF THESE LED DEVICES AT CLOSE RANGE.
6. DIALIGHT PART NUMBER: 521-9948



BIN	LIMITS (CHROMATICITY COORDINATES)				
		X	Y	Z	U
1	X	0.330	0.330	0.356	0.361
	Y	0.360	0.318	0.351	0.385
2	X	0.287	0.296	0.330	0.330
	Y	0.295	0.276	0.318	0.339
3	X	0.264	0.280	0.296	0.283
	Y	0.267	0.248	0.276	0.305
4	X	0.283	0.287	0.330	0.330
	Y	0.305	0.295	0.339	0.360

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.

SCALE 6:1 ALL DIM'S IN: INCHES (MM)		DRAWING NUMBER	REV
TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.008 ANGLES: ±1° FINISH:		C-17093	A
FSCM 83330		TITLE Ø 5.0 mm WHITE LED	
		MATERIAL	
		Dialight	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727
		SHEET OF	FAMILY TABLE: