

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT 2002 By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
ES	00		B1	REVISED ECR-11-021637	28OCT11	C.Z S.Y

D

D

C



C

B

B

A



A



SECT A-A
(SCALE 4:1)

NOTES

△COVER TAPE PEELING STRENGTH:1N(102gf)MAX
PEELING ANGLE:165°-180°
PEELING SPEED:300mm/MINUTE



NATURAL	PLASTIC	30.4	24.4	14.5	11.5	24	3500	15	1-1674976-5
NATURAL	PLASTIC	30.4	24.4	13.7	11.5	24	3500	14	1-1674976-4
NATURAL	PLASTIC	30.4	24.4	12.1	11.5	24	3500	12	1-1674976-2
NATURAL	PLASTIC	30.4	24.4	11.3	11.5	24	3500	11	1-1674976-1
NATURAL	PLASTIC	30.4	24.4	10.45	11.5	24	3500	10	1-1674976-0
NATURAL	PLASTIC	22.4	16.4	8.9	7.5	16	3500	8	1674976-8
NATURAL	PLASTIC	18.4	12.4	5.7	5.5	12	3500	4	1674976-4
NATURAL	PLASTIC	18.4	12.4	4.1	5.5	12	3500	2	1674976-2
HOUSING COLOR	REEL MATERIAL	REF W2	REF W1	C	B	A	QTY/REEL	POS	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.TSUJI CHK S.KAJINUMA APVD Y.YAMAMOTO	09APR03 09APR03 09APR03	TE Connectivity	
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-5830	APPLICATION SPEC	NAME TAB ASSEMBLY (H) SMT-TYPE WITH EMBOSS TAPE PACKAGE	
	0-PLC ± 1-PLC ± ±0.3 2-PLC ± ±3° 3-PLC ± 4-PLC ± ANGLES ±	0.8mm	PITCH WIRE TO BOARD MICRO TERMINATION (MT) CONNECTOR	SIZE A3	CAGE CODE 00779
MATERIAL 	FINISH 	WEIGHT 	CUSTOMER DRAWING	DRAWING NO C-1674976	RESTRICTED TO -
SCALE NTS				SHEET 1 of 2	REV B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT 2002 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE







DWN

APVD

ES

00

SEE SHEET 1



RECOMMENDED P.C.BOARD LAYOUT
(CONNECTOR MOUNTING SIDE)


0.085	NATURAL	14.2	11.2	15	1-1674976-5
0.08	NATURAL	13.4	10.4	14	1-1674976-4
0.07	NATURAL	11.8	8.8	12	1-1674976-2
0.065	NATURAL	11	8	11	1-1674976-1
0.06	NATURAL	10.2	7.2	10	1-1674976-0
0.05	NATURAL	8.6	5.6	8	1674976-8
0.03	NATURAL	5.4	2.4	4	1674976-4
0.02	NATURAL	3.8	0.8	2	1674976-2
WEIGHT(g)	COLOR	B	A	POSITION	PART NUMBER

NOTES

1. MATERIAL:
TAB HOUSING: THERMO PLASTIC UL94V-0
TAB CONTACT: COPPER ALLOY, Sn PLATING
SOLDER PEG: COPPER ALLOY, Sn PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- 0-PLC ±
1-PLC ± ±0.3
2-PLC ± ±3°
3-PLC ±
4-PLC ±
ANGLES ±
FINISH



DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

SEE TABLE

CUSTOMER DRAWING



TE Connectivity

NAME

TAB ASSEMBLY (H) SMT-TYPE
0.8mm PITCH WIRE TO BOARD
MICRO TERMINATION (MT) CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1674976

SCALE

NTS

SHEET

2 OF 2

REV

B1