

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

REV / 0720-0967-96


09SEP96

ME

TM

AMP
WIRE RANGE

UL E13288


LR7189
Certified12-10 AWG
SOLID OR STRANDED12-10 AWG
SOLID OR STRANDED12-10 AWG
SOLID OR STRANDED

1 STAMP AMP 12-10* LOCATE APPROX AS SHOWN

2. WIRE INSUL DIA, 3.81-5.84 [.150-.230]

3. TONGUE MATL THK, 1.02±0.05 [.040±.002]

2000	ONTAPE, REEL	2-321501-1
500	LOOSE PIECE	321501
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
170°C [338°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm [in]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, CU, SLV, CU PER
ASTM B152FINISH
TIN PLATE
PER MIL-T-10727

DWN	L OLMEDA	23JAN95
CHK	M ELLIS	23JAN95
APVD	S BORTNER	23JAN95
PRODUCT SPEC	UL486A	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

AMP AMP Incorporated
Harrisburg, PA 17105-3608NAME TERMINAL, RING,
DIAMOND GRIP,
WIRE SIZE, 12-10 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-321501

SCALE 6:1 SHEET 1 OF 1 REV C

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

CIRCULAR MIL AREA:
2.62mm²-6.64mm² [5180-13100]