




- 1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 5 SUPERSEDED BY 350765-5

PH BRZ GOLD 4			NYLON, NATURAL		350765-5
PH BRZ TIN			NYLON, NATURAL		350765-4
5 PH BRZ GOLD 2			NYLON, NATURAL		350765-3
CONTACT			HOUSING		PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.			TE Connectivity		
DIMENSIONS: mm [INCHES]			NAME 15 CIRCUIT UNIVERSAL MATE-N-LOK (TM) P.C. BOARD SOCKET HEADER ASSEMBLY		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			SIZE CAGE CODE DRAWING NO RESTRICTED TO		
0 PLC ±			A1 00779 350765		
1 PLC ±			CUSTOMER DRAWING		
2 PLC ±			SCALE 5:1 SHEET 1 OF 1 REV R1		
3 PLC ± 0.13 [.005]					
4 PLC ±					
ANGLES ±					
FINISH SEE TABLE					
WEIGHT					