

HF115F

MINIATURE HIGH POWER RELAY



File No.:E134517



File No.:116934



File No.:CQC08002028130



Features

- Low height: 15.7 mm
- 16A switching capability
- 5kV dielectric strength (between coil and contacts)
- Creepage distance: 10mm
- Meeting VDE 0700, 0631 reinforce insulation
- Product in accordance to IEC 60335-1 available
- Sockets available
- Plastic sealed and flux proofed types available
- UL insulation system: Class F available
- Environmental friendly product (RoHS compliant)
- Outline Dimensions: (29.0 x 12.7 x 15.7) mm

CONTACT DATA

Contact arrangement	1A, 1B, 1C	2A, 2B, 2C
Contact resistance	100mΩ max.(at 1A 6VDC)	
Contact material	See ordering info.	
Contact rating (Res. load)	12A/16A 250VAC	8A 250VAC
Max. switching voltage	440VAC / 300VDC	
Max. switching current	12A / 16A	8A
Max. switching power	3000VA / 4000VA	2000VA
Mechanical endurance	1 x 10 ⁷ ops	
Electrical endurance	1H3B type: 1 x 10 ⁵ ops (16A 250VAC, Resistive load, AgNi, Room temp., 1s on 9s off) 2H4B type: 1 x 10 ⁵ ops (8A 250VAC, Resistive load, AgNi, Room temp., 1s on 9s off)	

CHARACTERISTICS

Insulation resistance	1000MΩ (at 500VDC)						
Dielectric strength	Between coil & contacts	5000VAC	1min				
	Between open contacts	1000VAC	1min				
	Between contact sets	2500VAC	1min				
Surge voltage (between coil & contacts)	10kV (1.2 / 50μs)						
Operate time (at nomi. volt.)	15ms max.						
Release time (at nomi. volt.)	8ms max.						
Temperature rise (at nomi. volt.)	55K max.						
Shock resistance *	Functional	98m/s ²					
	Destructive	980m/s ²					
Vibration resistance *	10Hz to 150Hz 10g/5g						
Humidity	5% to 85% RH						
Ambient temperature	-40°C to 85°C						
Termination	PCB						
Unit weight	Approx. 13.5g						
Construction	Plastic sealed, Flux proofed						

Notes: 1) The data shown above are initial values.

2) * Index is not in relay length direction.

3) UL insulation system: Class F, Class B.

COIL

Coil power	Approx. 400mW
------------	---------------

COIL DATA

at 23°C

Nominal Voltage VDC	Pick-up Voltage VDC max.	Drop-out Voltage VDC min.	Max. Voltage VDC ¹⁾	Coil Resistance Ω
5	3.50	0.5	7.5	62 x (1±10%)
6	4.20	0.6	9.0	90 x (1±10%)
9	6.30	0.9	13.5	202 x (1±10%)
12	8.40	1.2	18	360 x (1±10%)
18	12.60	1.8	27	810 x (1±10%)
24	16.80	2.4	36	1440 x (1±10%)
48 ²⁾	33.60	4.8	72	5760 x (1±15%)
60 ²⁾	42.00	6.0	90	7500 x (1±15%)
110 ²⁾	77.00	11.0	165	25200 x (1±15%)

Notes: 1) Maximum voltage refers to the maximum voltage which relay coil could endure in a short period of time.

2) For products with rated voltage $\geq 48V$, measures should be taken to prevent coil overvoltage in order to protect coil in test and application (eg. Connect diodes in parallel).



HONGFA RELAY

ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

2014 Rev. 1.01

SAFETY APPROVAL RATINGS

VDE

Contact material	Specifications	Ratings	Ambient Temperature
AgCdO	HF115F....2(H;Z)(S)4(G)(F)	8A 250VAC	at 70°C
	HF115F....1H(S)(1;2)(G)(F)	12A 250VAC	at 70°C
		10A 250VAC	at 70°C
	HF115F....1Z(S)(1;2)(G)(F)	12A 250VAC	at 70°C
	HF115F....1H(S)3(G)(F)	16A 250VAC	at 70°C
		10A 250VAC	at 70°C
		9A 250VAC COSØ =0.4	at 70°C
AgNi	HF115F....1Z(S)3(G)(F)	16A 250VAC	at 70°C
		9A 250VAC COSØ =0.4	at 70°C
	HF115F....2(H;Z)(S)4B(G)(F)	5A 400VAC	at 85°C
		8A 250VAC	at 85°C
		12A 250VAC	at 85°C
		12A 250VAC	at 85°C
		16A 250VAC	at 85°C
	HF115F....1H(S)3B(G)(F)	9A 250VAC COSØ =0.4	at 70°C
		16A 250VAC (NO only)	at 85°C
		12A 250VAC	at 85°C
		9A 250VAC COSØ =0.4 (NO only)	at 70°C
		10(4)A 250VAC (NO only)	at 65°C
		12(2)A 250VAC (NO only)	at 65°C
AgSnO ₂	HF115F....2(H;Z)(S)4A(G)(F)	8A 250VAC	at 85°C
	HF115F....1(H;Z)(S)(1;2)A(G)(F)	12A 250VAC	at 85°C
	HF115F....1H(S)3A(G)(F)	16A 250VAC	at 85°C
		9A 250VAC COSØ =0.4	at 70°C
		16A 250VAC (NO only)	at 85°C
	HF115F....1Z(S)3A(G)(F)	9A 250VAC COSØ =0.4 (NO only)	at 70°C

UL/CUL

Version 1 or 2 (AgCdO)	12A 277VAC	Version 3 (AgSnO ₂)	16A 277 VAC
	1/2HP 250VAC		1/3HP 125VAC
	1/3HP 125VAC		1/2HP 250VAC
Version 1 or 2 (AgSnO ₂)	12A / 277VAC	Version 3 (AgNi)	B300
	B300		R300
	R300		16A 277VAC
Version 1 or 2 (AgNi)	12A 277VAC	Version 4 (AgCdO)	5FLA, 30LRA 250VAC
Version 3 (AgCdO)	16A 277 VAC		10A 250VAC
	9A 250VAC at 105°C		8A 277VAC
	1HP 250VAC		1/2HP 250VAC
	1/2HP 125VAC		1/4HP 125VAC
Version 4 (AgSnO ₂)	TV-5 125VAC	Version 4 (AgNi)	8A 277VAC
			8A 277VAC

Notes: 1) All values unspecified are at room temperature.

2) Only typical loads are listed above. Other load specifications can be available upon request.

ORDERING INFORMATION

Type	HF115F /	012	-1H	S	1	A	F	(XXX)
Coil voltage	5, 6, 9, 12, 18, 24, 48, 60, 110VDC							
Contact arrangement	1H: 1 Form A	1D: 1 Form B	1Z: 1 Form C					
	2H: 2 Form A	2D: 2 Form B	2Z: 2 Form C					
Construction ¹⁾²⁾	S: Plastic sealed		Nil: Flux proofed					
Version	1: 3.5mm 1 pole 12A	2: 5.0mm 1 pole 12A						
	3: 5.0mm 1 pole 16A	4: 5.0mm 2 pole 8A						
Contact material ³⁾	A: AgSnO ₂	B: AgNi	Nil: AgCdO	G: AgCdO+ Au plated				
	AG: AgSnO ₂ + Au plated		BG: AgNi+ Au plated					
Insulation standard	F: Class F	Nil: Class B						

Customer special code e.g. (335) stands for product in accordance to IEC 60335-1 (GWT)
(253) stands for Reflow soldering version, for 1 pole type

Notes:


- 1) We recommend flux proofed types for a clean environment (free from contaminations like H₂S, SO₂, NO₂, dust, etc.). We suggest to choose plastic sealed types and validate it in real application for an unclean environment (with contaminations like H₂S, SO₂, NO₂, dust, etc.).
- 2) Contact is recommended for suitable condition and specifications if water cleaning or surface process is involved in assembling relays on PCB.
- 3) For gold plated type, the min. switching current and min. switching voltage is 10mA 5VDC.

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT


Unit: mm

Outline Dimensions

3.5mm Pinning (HF115F/ □□□ -□□-□-1 -□□)




5mm Pinning (HF115F/ □□□ -□□-□-2/3/4 -□□)




Wiring Diagram (Bottom view)


3.5/5mm Pinning, 1 Pole, 12A, HF115F/ □□□ -1 □ -□ -1/2-□□



5mm Pinning, 1 Pole, 16A, HF115F/ □□□ -1 □ -□ -3-□□







5mm Pinning, 2 Pole, 8A, HF115F/ □□□ -2 □ -□ -4-□□



OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm


PCB Layout (Bottom view)




Remark: 1) In case of no tolerance shown in outline dimension: outline dimension ≤ 1 mm, tolerance should be ± 0.2 mm; outline dimension > 1 mm and ≤ 5 mm, tolerance should be ± 0.3 mm; outline dimension > 5 mm, tolerance should be ± 0.4 mm.
 2) The tolerance without indicating for PCB layout is always ± 0.1 mm.
 3) The width of the gridding is 2.52mm.

CHARACTERISTIC CURVES


MAXIMUM SWITCHING POWER



ENDURANCE CURVE



COIL OPERATING RANGE (DC) *



Remark:

1. Curve A: 2H4B type
 Curve B: 1H1B type(or 1H2B type)
 Curve C: 1H3B type
2. Test conditions:
 NO, Resistive load, 250VAC,
 Flux proofed, Room temp., 1s on 9s off.

Notes: * The use of a relay with an energising voltage other than the rated coil voltage may lead to reduced electrical life.

An energising voltage over the above range may damage the insulation of relay coil.

Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.