



# Amphenol® Solar Energy



Since 1932 Amphenol has been the interconnect technology provider of choice to industry leading companies throughout the world. With a broad and diverse product portfolio, Amphenol is able to develop the right solutions for our customers across the diverse segments of the rapidly expanding electronics market.

With dedicated employees working at 85 facilities in more than 30 countries, Amphenol has the unique advantage of having both diversified global reach while still being a focused organization.

**Amphenol can help you power the planet with the sun.**

### Amphoton PV-090729 and PV-090708 series

#### Features:

- Sealed design with high heat dissipation
- TÜV/UL approval



### Amphoton PV-090730 series

#### Features:

- Sealed design with high heat dissipation
- TÜV/UL dual approval



### Amphoton PV-090809 series


#### Features:

- Sealed design with high heat dissipation
- TÜV approval



**Technical Data**

Order No.	1	2	3	4	5
Part Number	PV-090729-003	PV-090729-006	PV-090808-001	PV-090808-002	PV-090808-003
Version	4 poles	4 poles	2 poles	3 poles	4 poles
Rated current	20A	20A	20A	20A	20A
Rated voltage	DC1000V(TÜV), DC600V(UL)	DC1000V(TÜV), DC600V(UL)	DC1000V(TÜV)	DC1000V(TÜV)	DC1000V(TÜV)
Number of bypass diodes	3	6	1	2	3
Connection cross-section	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12
Temperature range	-40°C up to +85°C	-40°C up to +85	-40°C up to +85°C	-40°C up to +85°C	-40°C up to +85°C
Protection degree	IP 65	IP 65	IP 65	IP 65	IP 65
Dimensions	150 x 130 x 26mm	150 x 130 x 26mm	89 x 80 x 22.5mm	89 x 80 x 22.5mm	108 x 95 x 25mm
Flame class	UL94-V0	UL94-V0	UL94-V0	UL94-V0	UL94-V0
Certificate	TÜV/UL	TÜV/UL	TÜV	TÜV	TÜV




D3	22.5	PV-090808-001
D2	80	PV-090808-002
D1	89	PV-090808-003
D3	25	PV-090729-003
D2	130	PV-090729-006
D1	150	
D3	25	PV-090808-003
D2	95	
D1	108	

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

**Technical Data**

Order No.	6	7	8
Part Number	PV-090730-002	PV-090730-003	PV-090730-006
Version	3 poles	4 poles	4 poles
Rated current	20A	20A	20A
Rated voltage	DC1000V(TÜV), DC600V(UL)	DC1000V(TÜV), DC600V(UL)	DC1000V(TÜV), DC600V(UL)
Number of bypass diodes	2	3	6
Connection cross-section	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12
Temperature range	-40°C up to +85°C	-40°C up to +85°C	-40°C up to +85°C
Protection degree	IP 65	IP 65	IP 65
Dimensions	103 x 58 x 16mm	103 x 58 x 16mm	103 x 58 x 16mm
Flame class	UL94-V0	UL94-V0	UL94-V0
Certificate	TÜV/UL	TÜV/UL	TÜV/UL




D3	16	PV-090730-002
D2	58	PV-090730-003
D1	103	PV-090730-006

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

**Technical Data**

Order No.	12	13
Part Number	PV-090809-001	PV-090809-002
Version	2 poles	3 poles
Rated current	20A	20A
Rated voltage	DC1000V(TÜV)	DC1000V(TÜV)
Number of bypass diodes	1	2
Connection cross-section	4mm <sup>2</sup> , AWG12	4mm <sup>2</sup> , AWG12
Temperature range	-40°C up to +85°C	-40°C up to +85°C
Protection degree	IP 65	IP 65
Dimensions	72 x 48 x 16mm	83 x 45 x 16.5mm
Flame class	UL94-V0	UL94-V0
Certificate	TÜV	TÜV



D3	16	PV-090809-001
D2	48	
D1	72	
D3	16.5	PV-090809-002
D2	45	
D1	83	

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

## How to order Amphoton Junction Box Assembly

**AP-**  
**1**  
1. Junction Box series

**4.0**  
**4**  
4. Connector/Cable cross section:  
2.5: 2.5mm<sup>2</sup> - 14 AWG  
4.0: 4.0mm<sup>2</sup> - 12 AWG  
6.0: 6.0mm<sup>2</sup> - 10 AWG


**90**  
**5**  
5. Cable length:  
Specify in CM

**03**  
**2**  
2. Junction Box Order No.

**P**  
**3**  
3. Cable type:  
P: Power-Link solar cable  
A: Armor-Link solar cable

AP- 03 / P / 4.0 / 90

1    2    3    4    5



### H4 connector

#### Features

- Self-locking to meet NEC2008
- Higher current
- Highest IP degree
- Lower power loss



### Ordering information

Part No.	Description	Wire range
PV-090506-000	H4 Cable Connector, Mated Pair	6.0mm <sup>2</sup> /10AWG
PV-090507-000	H4 Cable Connector, Mated Pair	2.5mm <sup>2</sup> /14AWG
PV-090508-000	H4 Cable Connector, Mated Pair	4.0mm <sup>2</sup> /12AWG



### PowerLink solar cable

#### Features

- PV-WIRE rated
- Better flame retardant (VW-1 rating)
- Better sunlight resistance
- Flexibility at low temperature
- Thermoplastic-insulated conductor



### Ordering information

Part No.	Description	Conductor cross section
PV-10-663060-004	PowerLink solar cable	2.5mm <sup>2</sup> /14AWG
PV-10-663060-005	PowerLink solar cable	4.0mm <sup>2</sup> /12AWG
PV-10-663060-006	PowerLink solar cable	6.0mm <sup>2</sup> /10AWG

## NORTH AMERICA:

### **Amphenol INDUSTRIAL OPERATIONS**

40-60 Delaware Street  
Sidney, New York 13838-1395 - USA  
Telephone: 1-520-285-5114 • 1-888-364-9011  
Fax: 1-520-397-7169

### **Amphenol INDUSTRIAL OPERATIONS Amphenol POWER SOLUTIONS**

34190 Riviera Drive  
Fraser, MI 48026 - USA  
Telephone: 1-586-294-7400 • Fax: 1-586-294-7402  
[www.radsok.com](http://www.radsok.com)

### **Amphenol TECHNICAL PRODUCTS INTERNATIONAL CO.**

2110 Notre Dame Avenue  
Winnipeg, MB Canada R3H 0K1  
Telephone: 1-204-697-2222 • Fax: 1-204-694-6164  
[www.tpi.com](http://www.tpi.com)

### **Amphenol STEWARD CABLE, INC.**

1921 Alta Vista - Midland, Texas 79706 - USA  
P.O. Box 11270 - Midland, Texas 79702 - USA  
Telephone: 1-432-687-2553 • Fax: 1-432-687-2278  
[www.stewardcable.com](http://www.stewardcable.com)

## EUROPE:

### **Amphenol TUCHEL ELECTRONICS GMBH**

August - Haeusser Strasse 10  
74080 Heilbronn, Germany  
Telephone: +49 7131 9290 • Fax: +49 7131 929 486  
[www.Amphenol.de](http://www.Amphenol.de)

### **Amphenol ITALY**

Via Barbaiana n. 5 - 20020 Lainate - Milano - Italy  
Telephone: 39-293-254-214 • Fax: 39-293-254-444

### **Amphenol SOCAPEX**

948 Promenade del - Arve - Bp29 - 74311 Thyez - France  
Telephone: 33-4 50 89 28 00 • Fax: 33-4 50 6 29 75

## ASIA:

### **Amphenol TECHNOLOGY (SHENZHEN) CO., LTD**

Block 5, Fu An 2nd Industrial Park,  
Dayang Road, Fuyong, Shenzhen - China 518103  
Telephone: 0755-2991-8389 • Fax: 0755-2991-8310  
[www.amphenol-industrial.com.cn](http://www.amphenol-industrial.com.cn)

### **Amphenol INTERCONNECT INDIA PRIVATE LIMITED**

105 Bhosari Industrial Area - Pune 411 026 - India  
Telephone: 91-20-712-0363/0463/0155  
Fax: 91-20-712-0581

### **Amphenol DAESHIN**

558 Sosa SongNea Bucheon-city, Kyunggi-DO  
Korea 420-130  
Telephone: 82-32-610-3800  
Fax: 82-32-673-2507/665-6219

### **Amphenol SINGAPORE**

300 Beach Road #34-06 The Concourse  
Singapore 199555 - Singapore  
Telephone: (65) 6294-2128 • Fax: (65) 6294-3522

