







VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR
HEREWITH IS NOT TO BE REPRODUCED, USED OR
DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT
THE PERMISSION OF VICOR CORP.



REV.	DESCRIPTION		DATE	APPROVED
1	RELEASED PER E0230307	PEI	07/11/02	JMR
2	REVISED PER E080070	SA	01/15/08	REJH
3	REVISED PER E091753	JS	09/29/09	REJH
4	REVISED PER E092276	JS	12/30/09	REJH
5	REVISED PER E120065	VSS	01/20/12	KUK



DASH NO.	SOCKET BODY LENGTH INCH/MM	DIA "A" INCH/MM	DIA "B" INCH/MM	INPUT	OUTPUT	KIT #
-01	.100/2.54	.280/7.11	.280/7.11	18378	18390	18368
-02	.135/3.43	.315/8.00	.315/8.00	18379	18391	18369
-03	.160/4.06	.340/8.64	.340/8.64	21539	21544	21511

NOTE:

1. MATERIALS: INMATES: PPS RYTON 7
SOCKETS: BE-CU #25, Au PLATED.
2. FULLY SEAT SOCKET INTO INMATE HEADER.
3. ROHS COMPLIANT PER CST-0001 LATEST REVISION.



DRAWN BY		DATE		 VICOR		SWD	
LAP NGUYEN		6/99					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE : INCH [MM]				DWG, VI-800 INMATE/SOCKET, LN			
TOLERANCES ARE: DECIMALS ANGLES X.XX [X.X] +0.01 [0.25] 11° X.XXX [X.XX] +0.005 [0.127]							
THIRD ANGLE PROJECTION							
 DO NOT SCALE DRAWING		SIZE D 67131	CAGE CODE	DWG NO 20030-XX	REV 5		
		SCALE 4:1				SHEET 1 OF 1	