

GaAs MMIC SP3T NON-REFLECTIVE SWITCH, DC - 3.5 GHz

Typical Applications

The HMC245QS16 is ideal for:

- Basestation Infrastructure
- CATV / DBS
- Wireless Local Loop
- Test Equipment

Features

Low Insertion Loss: 0.5 dB @ 2.0 GHz

Non-Reflective Design


Integrated 2:3 TTL Decoder

“All Off” Isolation State

Single Positive Supply: Vdd = +5V

16 Lead QSOP SMT Package

Functional Diagram



General Description

The HMC245QS16 is a low cost non-reflective SP3T switch in a 16-lead QSOP surface mount package. Covering DC to 3.5 GHz, the switch offers 30 to 40 dB isolation and a low insertion loss of 0.5 dB. A 2:3 TTL/CMOS compatible decoder is integrated on the switch requiring only 2 control lines and a single +5V bias to select each path, replacing 6 control lines normally required by GaAs SP3T switches.


Electrical Specifications,

$T_A = +25^\circ \text{C}$, For TTL Control and Vdd = +5V in a 50 Ohm System


Parameter	Frequency	Min.	Typ.	Max.	Units
Insertion Loss	DC - 2.0 GHz		0.5	0.8	dB
	DC - 3.0 GHz		0.6	0.9	dB
	DC - 3.5 GHz		0.7	1.0	dB
Isolation	DC - 1.0 GHz	40	44		dB
	DC - 2.0 GHz	35	39		dB
	DC - 2.5 GHz	31	35		dB
	DC - 3.5 GHz	26	30		dB
Return Loss	“On State”	DC - 1.5 GHz	20		dB
		DC - 3.5 GHz	17		dB
Return Loss RF1 - 3	“Off State”	0.3 - 3.5 GHz	12		dB
		0.5 - 3.5 GHz	15		dB
Input Power for 1 dB Compression	0.3 - 2.5 GHz	23	26		dBm
	0.3 - 3.5 GHz	22	25		dBm
Input Third Order Intercept (Two-tone Input Power = +7 dBm each tone)	0.3 - 2.5 GHz	44	48		dBm
	0.3 - 3.5 GHz	40	44		dBm
Switching Characteristics	0.3 - 3.5 GHz	tRISE, tFALL (10/90% RF)	40		ns
		tON, tOFF (50% CTL to 10/90% RF)	150		ns

GaAs MMIC SP3T NON-REFLECTIVE SWITCH, DC - 3.5 GHz


Insertion Loss vs. Temperature




Isolation




Return Loss




Off State Isolation



0.1 and 1 dB Input Compression Point



Input Third Order Intercept Point



GaAs MMIC SP3T NON-REFLECTIVE SWITCH, DC - 3.5 GHz

Absolute Maximum Ratings

Bias Voltage Range (Port Vdd)	+7.0 Vdc
Control Voltage Range (A & B)	-0.5V to Vdd +1 Vdc
Channel Temperature	150 °C
Thermal Resistance (Insertion Loss Path)	210 °C/W
Thermal Resistance (Terminated Path)	250 °C/W
Storage Temperature	-65 to +150 °C
Operating Temperature	-40 to +85 °C
Maximum Input Power Vdd = +5 Vdc	+20 dBm (0.05 - 0.5 GHz) +27 dBm (0.5 - 3.5 GHz)

Bias Voltage & Current


Vdd Range= +5.0 Vdc ±10%		
Vdd (Vdc)	Idd (Typ) (mA)	Idd (Max) (mA)
+5.0	3.0	6.0

Truth Table

Control Input		Signal Path State
A	B	RF COM to:
Low	Low	RF1
High	Low	RF2
Low	High	RF3
High	High	All Off

TTL/CMOS Control Voltages

State	Bias Condition
Low	0 to +0.8 Vdc @ 5 uA Typ.
High	+2.0 to +5.0 Vdc @ 70 uA Typ.





***GaAs MMIC SP3T NON-REFLECTIVE
SWITCH, DC - 3.5 GHz***

Mechanical drawing of the HMC245 package showing dimensions and pin numbers. The package is a square component with pins on all four sides. The top and bottom pins are numbered 9 to 16 and 1 to 8 respectively. The drawing includes dimensions in inches and millimeters, and a lot number field labeled 'XXXX'.

Dimension	Value (inches)	Value (millimeters)
Top Pin Pitch	.197	5.00
Top Pin Width	.189	4.80
Bottom Pin Pitch	.197	5.00
Bottom Pin Width	.189	4.80
Left Pin Pitch	.158	4.00
Left Pin Width	.150	3.80
Right Pin Pitch	.244	6.20
Right Pin Width	.228	5.80

Pin Numbers: 16, 15, 14, 13, 12, 11, 10, 9 (top); 1, 2, 3, 4, 5, 6, 7, 8 (bottom).

Lot Number: XXXX




7. ALL GROUND LEADS MUST BE SOLDERED TO PCB RF GROUND.

Pin Number	Function	Description	Interface Schematic
1, 6, 12, 14	RF3, RF2, RF1, RFC	This pin is DC coupled and matched to 50 Ohms. Blocking capacitors are required.	
2 - 5, 7, 11, 13, 15, 16	GND	This pin must be connected to PCB RF ground to maximize isolation.	
8	Vdd	Supply Voltage +5.0 Vdc $\pm$ 10%	
9	B	See truth table and control voltage table.	
10	A	See truth table and control voltage table.	

GaAs MMIC SP3T NON-REFLECTIVE SWITCH, DC - 3.5 GHz

Evaluation PCB



List of Material

Item	Description
J1 - J4	PC Mount SMA RF Connector
J5 - J8	DC Pin
C1 - C4	100 pF Capacitor, 0402 Pkg.
C5	10k pF Capacitor, 0603 Pkg.
U1	HMC245QS16 SP3T Switch
PCB*	106536 Evaluation PCB
* Circuit Board Material: Rogers 4350	

The circuit board used in the final application should be generated with proper RF circuit design techniques. Signal lines at the RF port should have 50 ohm impedance and the package ground leads should be connected directly to the ground plane similar to that shown above. The evaluation circuit board shown above is available from Hittite Microwave Corporation upon request.

GaAs MMIC SP3T NON-REFLECTIVE SWITCH, DC - 3.5 GHz

Notes: