






SCALE 2.000





SCALE 2.000



SECTION R-R



spec ref *		dr		wcadmin	2007/05/11	projection			MM	size	A3	scale	1.000		
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Qin De-Feng				2012/10/23	ecn no					ELX-DG-011871-1
				chr	-				-	rel level					Released
				appr	Pei-Ming Zheng				2012/10/24	product family					
surface  ISO 1302	linear	0.X	±0.2		title	PF TYPE ASS'Y MICRO TCA				dwg no	10058831		rev	J	
		0.XX	±0.15												
		0.XXX	±0.08												
		angular	0°	±5°	www.fci.com	cat. no.	*	Product - Customer Drw				sheet 1 of 4			



RECOMMENDED PCB LAYOUT
(SEE PICMG MICROTCA BASE SPECIFICATION FOR DETAIL)

REMARK:FUNCTIONAL CONTACT PIN LIST OF MATING INTERFACE

POWER	2,9,18,27,42,57,72,84
GROUND	1,7,10,13,16,19,22,25,28,31,34,37,40,43,46,49,52,55,58,61,64,67,70,73,76,79,82,85,86,89,92,95,98,101,104,107,110,113,116,119,122,125,128,131,134,137,140,143,146,149,152,155,158,161,164,170
GENERAL PURPOSE	3,4,5,6,8,17,26,41,56,71,83,165,166,167,168,169
DIFFERENTIAL PAIRS	11/12,14/15,20/21,23/24,29/30,32/33,35/36,38/39,44/45,47/48,50/51,53/54,59/60,62/63,65/66,68/69,74/75,77/78,80/81,87/88,90/91,93/94,96/97,99/100,102/103,105/106,108/109,111/112,114/115,117/118,120/121,123/124,126/127,129/130,132/133,135/136,138/139,141/142,144/145,147/148,150/151,153/154,156/157,159/160,162/163

spec ref	*	dr	wcadmin	2007/05/11	projection	MM	size	A3	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Qin De-Feng	2012/10/23			ecn no	ELX-DG-011871-1		
ISO 406		chr	-	-			rel level	Released		
ISO 1101		appr	Pei-Ming Zheng	2012/10/24	product family					
surface	linear	0.X	±0.2	FCI	PF TYPE ASS'Y	dwg no	10058831	rev	J	
		0.XX	±0.15							
		0.XXX	±0.08							
ISO 1302	angular	0°	±5°	www.fci.com	cat. no.	*	Product - Customer Drw	sheet 2 of 4		



Copyright FCI.

A

B

C



D

A

B

C

D



DETAIL A
SCALE 20.000

SCALE 4.000

RECOMMENDED MODULE LAYOUT
(SEE PICMG ADVANCED MEZZANINE CRAD BASE SPECIFICATION FOR DETAIL)

spec ref *				dr	w wadmin	2007/05/11	projection 	MM 	size	A3	scale	1.000	
tolerance std				eng	Qin De-Feng	2012/10/23			ecn no				ELX-DG-011871-1
ISO 406 ISO 1101				chr	-	-			rel level				Released
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr	Pei-Ming Zheng	2012/10/24	product family						
surface ISO 1302	linear	0.X	±0.2		title PF TYPE ASS'Y MICRO TCA				dwg no	10058831		rev J	
		0.XX	±0.15										
		0.XXX	±0.08										
angular	0°	±5°	www.fci.com	cat. no.				*	Product - Customer Drw		sheet 3 of 4		

