





LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN
						APVD
		C2		REVISED PER ECO-11-004587	11MAR2011	RK
		D		REVISED ECR-11-020698	25OCT2011	C.D


- I AS SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED:



- 1 HEATSINK MARTEIAL: ALUMINUM ALLOY
- 2 FINISH: ANNODIZED
- 3 2-56 SHOULDER BOLT AND SPRING PRE-ASSEMBLED AND HELD IN PLACE WITH CLIP
- 4 FULL ROUND PERMITTED ON TOP OF HEATSINK FINS



4	4	E-CLIP	4
4	4	SPRING	3
4	4	2-56 SHOULDER SCREW	2
1	-	HEAT SINK (22 FINS)	1
-	1	HEAT SINK (36 FINS)	
-2	-1	DESCRIPTION	ITEM NO.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BM 3-5-09		 TE Connectivity			
		CHK B. STRATTON 3-5-09					
DIMENSIONS: mm (inch)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EARY 5-11-09		NAME	
		0 PLC ±-		PRODUCT SPEC		HEAT SINK ASSEMBLY 100 GIG PLUGGABLE -	
		1 PLC ±0.5		-			
		2 PLC ±0.25		APPLICATION SPEC			
		3 PLC ±0.125		-			
4 PLC ±0.0001		ANGLES ±1°		-		SIZE	
MATERIAL		FINISH		WEIGHT		CAGE CODE	
				-		DRAWING NO	
				CUSTOMER DRAWING		RESTRICTED TO	
						A200779	
						C=1963856	
						SCALE	
						1.000	
						SHEET	
						1 OF 2	
						REV	
						D	

LOC		DIST		REVISIONS						
P	LTR	DESCRIPTION				DATE	DWN	APVD		
-	-	SEE SHEET 1				-	-	-		



DETAIL B
SCALE 12.000

- 2 AS SHOWN



SEE DETAIL B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25OCT2011		TE Connectivity HEAT SINK ASSEMBLY 100 GIG PLUGGABLE						
DIMENSIONS:		CHK	25OCT2011								
mm(inch)		APVD	25OCT2011								
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± 1 PLC ±0.5 2 PLC ±0.25 3 PLC ±0.125 4 PLC ±0.0001 ANGLES ±1°		PRODUCT SPEC							
		FINISH		APPLICATION SPEC							
MATERIAL		-		WEIGHT	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-		-		-		A200779		C=1963856		-	
CUSTOMER DRAWING				SCALE		1.000		SHEET		2 OF 2	
										REV D	