



DIMENSIONS



TERMINATION



TIN LEAD PART NUMBER

PART NUMBER

86094647113785000E1


LEAD FREE PART NUMBER

PART NUMBER

86094647113785E1LF

P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size A3		Scale 1.5
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR	LINEAR	0.X	±0.1	size	ECN L506-0095
Dr ROUILLARD 2001/02/06		0.XX	±0.1	0.XXX	±0.1	ECN	Spec ref -
Eng TARON 2001/02/06		0.XX	±0.1	0.XXX	±0.1	ECN	Spec ref -
Chr LEGARE 2001/02/06		0.XX	±0.1	0.XXX	±0.1	ECN	Spec ref -
Appr LEGARE 2001/02/06		0.XX	±0.1	0.XXX	±0.1	ECN	Spec ref -
Product family		DIN 8609		Spec ref -		Rev.	
FCI		title		STANDARD MALE 3 ROW		Rev.	
64 CONTACTS		catag no		C-8609-0933		Rev.	
CUSTOMER		sheet 1 of 1		Rev.		C	

rev	ecn no	dr	date
A	-	-	2001/02/06
B	LS05-001	JTA	2005/03/05
C	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-