

LOC		DIST						REVISIONS		
CM		53		P		F		ZONE	LTR	DESCRIPTION
								AD1	REV PER	ECR-15-007412
									DATE	05-20-15
									APPD	SC
										DZ







- 1

NICKEL UNDER PLATE 0.00127 [0.000050] MIN THICK ON ENTIRE PART WITH 0.00076 [0.000030] MIN GOLD IN LOCALIZED PLATE AREA.
- 2

WIRE RANGE: 0.3 – 0.84mm² (24–18 AWG).
- 3

INSULATION RANGE: 2.79 [.110] MAX. DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

1	0.25 [.010] BRASS	350418-5
PRE-TIN	0.25 [.010] BRASS	350418-1
FINISH	MATERIAL	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ±0.13 [.005] ANGLES ± -		DR 9-3-92 N. GANNON CHK 9-3-92 R. SWING APPD 9-8-92 C. CASH APPD 9-8-92 C. CASH	AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL		PRODUCT SPEC	NAME		
SEE TABLE		APPLICATION SPEC	.093 PIN COMMERICAL PIN AND SOCKET		
FINISH		WEIGHT	SIZE D	CAGE CODE 00779	DRAWING NO C-350418
			SCALE 5:1	SHEET 10F 1	